




Connectors > Automotive Connectors > Connector Accessories > Other Connector Accessories



Automotive Connector Accessory Type: **Blind Plug**

Primary Product Material: **PA66**

Primary Product Color: **Blue**

Operating Temperature Range: **-40 – 125 °C, -40 – 125 °C [-40 – 257 °F, -40 – 257 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Blind Plug
-------------------------------------	------------

Body Features

Primary Product Material	PA66
Primary Product Color	Blue

Usage Conditions

Operating Temperature Range	-40 – 125 °C, -40 – 125 °C[-40 – 257 °F][-40 – 257 °F]
-----------------------------	--

Industry Standards

UL Flammability Rating	None
------------------------	------

Packaging Features

Packaging Quantity	30000
Packaging Method	Bag

Other

Serviceable	No
-------------	----



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-M4595-CH8172
MCON, CONNECTOR HOUSING


TE Part # 1924939-1
PLUG ASSY, 96P GPEC II KEY A RIGHT EXIT

TE Part # 1-2005475-2
PCU SLD 105P PLUG ASSY(A-RH)

TE Part # 1452421-3
58 POS. CONNECTOR COVER 90 ASSY




TE Part # 1-2344950-1
95POS, HYBRID, REC HSG, ASSY,
COD A



TE Part # 1-2344951-2
104POS, MCON 1.2, REC HSG, ASSY,
COD A



TE Part # 2-1564285-8
58POS, MIXED,REC HSG,ASSY




TE Part # 2-2344950-1
95POS, HYBRID, REC HSG, ASSY,
COD B



TE Part # 8-1452423-7
96 POS. PCM CPNECTOR



TE Part # 9-1452415-5
58 POS MIXED, MCON CONNECTOR



TE Part # 1-1452415-5
58 POS FEMALE ASSY CONNECTOR



TE Part # 1-1563172-4
58POS, MIXED,REC HSG,ASSY



TE Part # 1-1564284-1
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 1-1564284-7
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 1-1564284-8
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 1-1564284-9
96POS,MCON-1.2 CB,REC HSG,ASSY



TE Part # 1-1564285-4
58POS, MIXED,REC HSG,ASSY



TE Part # 1-1564285-5
58POS, MIXED,REC HSG,ASSY



TE Part # 1-1564285-7
58POS, MIXED,REC HSG,ASSY




TE Part # 2-1563173-1
96POS,MCON-1.2 CB,REC HSG,ASSY

Also in the Series | MCON 1.2mm



Automotive Connector Caps & Covers
(9)



Automotive Connector Locks &
Position Assurance(9)



Automotive Housings(5)



Automotive Seals & Cavity Plugs(1)



Automotive Terminals(11)



Insertion & Extraction Tools(5)




Other Automotive Connector Accessories(4)

Also in the Series | MCON Interconnection System



Automotive Connector Caps & Covers (24)



Automotive Connector Locks & Position Assurance(11)



Automotive Headers(1)



Automotive Housings(288)



Automotive Seals & Cavity Plugs(4)



Automotive Terminals(114)



Insertion & Extraction Tools(31)



Other Automotive Connector Accessories(6)

Customers Also Bought



TE Part #1452503-1
MCON, RECEPTACLE AND TAB



TE Part #SRK-BS-FL-90-001
BKSHL, FULL, BLK, RA, NW 22/26



TE Part #1452421-1
58 POS. CONNECTOR COVER 90 ASSY



TE Part #1452389-1
COVER ASSY 96 POS.



TE Part #1452408-1
2-NDRY F58 POS. CONNECTOR



TE Part #1452388-1
2 LOCKING DEV1.2



TE Part #1452416-1
58POS CONNECTOR COVER 180 ASSY



TE Part #1452409-2
SECONDARY LOCK FOR 58 POS CONN



Documents

Product Drawings

BLIND PLUG FOR MCON 1.2 CB (1.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1452424-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1452424-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1452424-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English