




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board, Wire-to-Panel, Wire-to-Wire**

Number of Positions: **6**

Centerline (Pitch): **4.2 mm [.165 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Power Positions	0
Number of Signal Positions	6
Number of Rows	3

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Contact Features

Contact Current Rating (Max)	9 A
Contact Retention Within Housing	With
Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Panel Mount
Mating Retention	With
Mating Retention Type	Positive Lock

Housing Features

Centerline (Pitch)	4.2 mm[.165 in]
Housing Color	Black
Housing Material	PA 66

Dimensions

Wire Size	.12 – .8 mm ²
Row-to-Row Spacing	4.19 mm[.165 in]
Width	21.34 mm[.84 in]
Accepts Wire Insulation Diameter Range	2.92 mm[.115 in]
Height	12.95 mm[.51 in]
Length	21.34 mm[.84 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard Number	E28476
Agency/Standard	CSA, UL
UL Rating	Recognized
CSA File Number	LR7189

Packaging Features

Packaging Method	Box
Packaging Quantity	1500

Product Compliance




For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: 1,6,7,8,9,14,15,16,17,17,18,18-dodecachloropentacyclo [12.2.1.16,9.02,13.05,10]octadeca-7,15-diene (Dechlorane Plus) (20% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1-640510-0
06P MR II CAP HSG V0 RED




TE Part # 640500-3
06P MR HDR ASSY V0 RED



TE Part # 640500-5
06P MR HDR ASSY V0 RED




TE Part # 640500-6
06P MR HDR ASSY V0 RED




TE Part # 640500-1
06P MR HDR ASSY V0 RED




TE Part # 1-350373-9
06P STR/REL HNGD




TE Part # 2-640500-2
06P MR HDR ASSY V0 RED LF



TE Part # 2-640500-4
06P MR HDR ASSY V0 RED LF




TE Part # 640500-2
06P MR HDR ASSY V0 RED



TE Part # 1318699-2
MR HDR ASSY 6P COATING

Also in the Series | AMP MR



Board-to-Board Connector Housings(2)



Board-to-Board Jumpers & Shunts(4)



Insertion & Extraction Tools(1)



Power Cable Assemblies(1)




Rectangular Power Connectors(12)




Wire-to-Board Connector Assemblies
& Housings(4)


Customers Also Bought




TE Part #1-640508-0
03P MR II CAP HSG V0 RED




TE Part #1-640510-0
06P MR II CAP HSG V0 RED




TE Part #1-640518-0
03P MR II PLUG HSG V0 RED




TE Part #1-640519-0
04P MR II PLUG HSG V0 RED




TE Part #1-640521-0
09P MR II PLUG HSG V0 RED




TE Part #1-640507-0
02P MR II CAP HSG




TE Part #1-640517-0
02P MR II PLUG HSG



TE Part #794000-1
MR RECEPTACLE PTPPHBZ



TE Part #1-640509-0
04P MR II CAP HSG V0 RED



TE Part #1-640511-0
09P MR II CAP HSG V0 RED

Documents

Product Drawings

06P MR II PLUG HSG V0 RED

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-640520-0_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-640520-0_F.3d_igs.zip

English

Customer View Model

ENG_CVM_1-640520-0_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_1-640520-0_021920182238_dmtec



English

[MD_1-640520-0_021920182238_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

AMP* MINIATURE RECTANGULAR II (MRII) CONNECTORS

English

Agency Approvals

[Agency Approval Document](#)

English