



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **2**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Natural**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	2
--	---

Body Features

Crimp Terminal Housing Housing Color	Natural
Crimp Terminal Housing Mating Retention	With
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)
---------------------------------------	----------------------------

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Length	31.5 mm[1.24 in]
Crimp Terminal Housing Centerline	7.4 mm[.291 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	3000
Crimp Terminal Housing Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 170340-1 FF 250 TAB 20-14AWG BR WITHOUT LATCH	 TE Part # 170341-3 FF 250 TAB 14-12AWG PTBR WITHOUT LATCH	 TE Part # 170349-2 FF 250 TAB 22-20AWG TPBR WITHOUT LATCH	 TE Part # 170340-3 FF 250 TAB 20-14AWG PTBR WITHOUT LATCH
 TE Part # 170341-1 FF 250 TAB 14-12AWG BR WITHOUT LATCH	 TE Part # 1-626065-2 FF 110 2P HOUSING TAB NATURAL PA6.6 V-0	 TE Part # 626065-5 HOUSING 2P .110 FASTIN-ON TAB	 TE Part # 170349-1 FF 250 TAB 22-20AWG BR WITHOUT LATCH
 TE Part # 1-180907-6 FF 250 REC HSG 2P NYLON NAT	 TE Part # 9-144836-5 DOUBLE LOCKING 5 MM HOUSING TAB PA66	 TE Part # 1-144836-5 HOUSING TAB 5MM 5 P BROWN	 TE Part # 180908-3 FF 250 TAB HSG 2P NYLON BLUE
 TE Part # 5-144835-3 HOUSING TAB 5MM 3 P GREEN	 TE Part # 6-316441-6 FF 187 PLUG 8P ASSY LIGHT GRAY	 TE Part # 927357-1 FF 110 2P HOUSING PA66 NATURAL	 TE Part # 927670-1 FF 203 TAB HSG 16P NYLON NAT

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(216)



Insertion & Extraction Tools(2)



PCB Terminals(2)



Quick Disconnects(258)

Customers Also Bought



TE Part #1-1971775-3
POWER TRIPLE LOCK STD TEMP
PLUG



TE Part #1443996-4
COVER, 60 POS, W/O FUSE HLDR/NO
EXT TEXT



TE Part #1241809-2
UMNL ST-SOCK,A-P 3P



TE Part #926886-3
UNIV.M-N-L.PIN



TE Part #1-1703062-2
CAP, 2 CIRCUIT , UNIVERSAL MATE-
N-LOK



TE Part #160389-3
250 FASTON,REC.,24-17 AWG,PNST



TE Part #1-1376390-5
Glow Wire Power Key Plug



TE Part #1-962375-1
TIMER, CONNECTOR HOUSING



TE Part #1-1803074-0
ANVIL,COMBINATION, END FEED



TE Part #1393583-2
C42334A 228A441=RP GEHAEUSE

Documents

Product Drawings

FF 250 TAB HSG 2P NYLON NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-180908-0_AB.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-180908-0_AB.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-180908-0_AB.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[White Paper: Nylon Discoloration](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_1-180908-0_03032018748_dmtec](#)

English

[MD_1-180908-0_03032018748_dmtec](#)

English

Agency Approvals

[UL Report](#)

English