




Connectors > Circular Connectors > Circular Connector Accessories > Unscreened Circular Connector Backshells & Clamps



Backshell & Clamp Accessory Type: **Cable Clamp**  
Compatible With Circular Connector Shell Size: **17**  
Body Orientation: **Straight**  
Accepts Cable Diameter (Max): **17.86 mm [ .703 in ]**  
Protective Cover: **Without**

Features

Product Type Features

Product Type	Accessory
Backshell & Clamp Accessory Type	Cable Clamp
Protective Cover	Without

Body Features

Cable Clamp Material	Thermoplastic
Cable Clamp Flammability Rating	UL 94V-1
Cable Clamp Color	Black

Mechanical Attachment

Screw & Hole Thread Size	15/16-20 UNEF-2B
--------------------------	------------------

Housing Features

Body Orientation	Straight
------------------	----------

Dimensions

Accepts Cable Diameter (Max)	17.86 mm[.703 in]
------------------------------	-------------------

Operation/Application

Compatible With Circular Connector Shell Size	17
---	----

Packaging Features

Packaging Quantity	1
--------------------	---



Packaging Method

Individual

Other

Comment	Cable clamps can be threaded directly onto plugs or receptacles, or onto back-shell extenders.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | AMP CPC

Circular Connector Adapters(7)	Circular Connector Boots & Strain Relief(6)	Circular Connector Caps & Covers(16)	Circular Connector Hardware(3)
Circular Connector Keying Plugs(2)	Circular Connector Seals(36)	Circular Power Connectors(513)	Insertion & Extraction Tools(1)
Power Contacts(5)	Sealing Sleeves(2)	Unscreened Circular Connector Backshells & Clamps(56)	

Customers Also Bought

TE Part #183040-1 CPC EMEA	TE Part #1-66099-5 TYPE III CONTACTS LP	TE Part #1546348-2 CPC CABLE CLAMPS	TE Part #1-641737-1 04P CMNL HDR ASSY R/A V0
TE Part #1625875-5 CBT 1/4 5% 100R	TE Part #1-2176083-4 EP 5W (S) 1K5 5%	TE Part #1-206062-3 CPC cable clamp, size 11	TE Part #CB5407-000 SST-6-04/FR/97



Documents

Product Drawings

CABLE CLAMP KIT, BULK PKG

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-206322-1\_S.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-206322-1\_S.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-206322-1\_S.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

MD\_1-206322-1\_022720182353\_dmtec

English

MD\_1-206322-1\_022720182353\_dmtec

English