



Connectors > Automotive Connectors > Connector Housings > MQS, CONNECTOR HOUSING



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **.63 mm [.025 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **8**

Centerline (Pitch): **2.54 mm [.1 in]**

[All MQS, CONNECTOR HOUSING \(575\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	8
Number of Rows	2

Electrical Characteristics

Operating Voltage	24 VDC
Nominal Voltage Architecture	12 V, 24 V

Body Features

Cable Exit Angle	180°
Body Material	PA GF
Primary Product Color	Black

Contact Features

Mating Tab Width	.63 mm[.025 in]
------------------	-----------------



Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Width	11.3 mm[.445 in]
Product Length	11.3 mm[.445 in]
Product Height	16.6 mm[.654 in]
Row-to-Row Spacing	3 mm, 3.2 mm[.118 in][.126 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C[158 °F][167 °F] [176 °F][185 °F]
Operating Temperature Range	-25 – 85 °C[-13 – 185 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	2000
Packaging Method	Box

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021
(211)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

Also in the Series | MQS

Automotive Connector Caps & Covers
(133)

Automotive Connector EMC Shielding
(2)

Automotive Connector Locks & Position Assurance(29)

Automotive Headers(207)



Automotive Housings(498)

Automotive Seals & Cavity Plugs(26)

Automotive Terminals(98)

Data Connectivity Headers(1)

Insertion & Extraction Tools(42)

Other Automotive Connector Accessories(13)

Customers Also Bought

TE Part #1-968562-2
MQS, CONNECTOR HOUSING

TE Part #1241846-2
TIMER, RECEPTACLE AND TAB

TE Part #1379662-1
TH/.025 CONNECTOR SYSTEM, HOUSING

TE Part #106455-4
FF 110 PLUG HSG 8P.

TE Part #1379101-1
COV+LEV MQS 18W 90DEG BLK

TE Part #1-1534096-1
MQS ABDECKKAPPE2X6P

TE Part #1-1534097-1
MQS COVER 2X8P

TE Part #1355528-2
MPQ 2.KONT-SICHNG8P

TE Part #1-22278-9
SPRING,COMPRESSION

Documents



Product Drawings

8POS MQS REC

English

CAD Files

Customer View Model

ENG_CVM_1745000-3_B.3d_igs.zip

English

Customer View Model

ENG_CVM_1745000-3_B.3d_stp.zip

English

Customer View Model

ENG_CVM_1745000-3_B.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Micro Quadlok Interconnection System (MQS)

English

Product Specifications

Application Specification

English

Application Specification

English