




Connectors > Automotive Connectors > Connector Housings > MULTILOCK, CONNECTOR HOUSING



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **1.8 mm [ .071 in ]**

Connector System: **Wire-to-Wire**

Number of Positions: **20**

Centerline (Pitch): **3.5 mm, 5.5 mm [ .138 in, .217 in ]**

[All MULTILOCK, CONNECTOR HOUSING \(577\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	20
Number of Rows	2

Electrical Characteristics

Operating Voltage	12 VDC
Nominal Voltage Architecture	12 V

Body Features

Cable Exit Angle	180°
Body Material	PBT
Primary Product Color	Yellow

Contact Features

--	--



Mating Tab Width	1.8 mm[.071 in]
------------------	-----------------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	3.5 mm, 5.5 mm[.138 in][.217 in]
--------------------	----------------------------------

Dimensions

Product Width	45.8 mm[1.803 in]
Product Length	21.6 mm[.85 in]
Product Height	26.05 mm[1.026 in]
Row-to-Row Spacing	10.7 mm, 2.54 mm, 8.31 mm[.1 in][.327 in][.421 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	50
--------------------	----

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

<p>TE Part # CAT-M9194-T273 MULTILOCK, RECEPTACLE AND TAB</p>	<p>TE Part # CAT-M9194-CH8172 MULTILOCK, CONNECTOR HOUSING</p>	<p>TE Part # CAT-SIGH262 SIGNAL HEADER</p>	<p>TE Part # CAT-LMPH9507 LOW &amp; MEDIUM POWER HEADER</p>
<p>TE Part # 1-174936-1 070 MLC W-W CAP HSG 20P F/A</p>	<p>TE Part # 345208-1 070 SERIES RECEPT.</p>	<p>TE Part # 175026-1 070 REC CONTACT L.P 24-22</p>	<p>TE Part # 174936-6 070 MLC W-W CAP HSG 20P</p>



TE Part # 2-174960-1  
070 MLC CAP ASSY V 20P NATURAL

TE Part # 9-1438309-1  
34 POS CAP HOUSING ASSY, H-TYP

Also in the Series | Multilock Connector System

Automotive Connector Caps & Covers (16)

Automotive Connector EMC Shielding (1)

Automotive Connector Locks & Position Assurance(2)

Automotive Headers(138)

Automotive Housings(576)

Automotive Seals & Cavity Plugs(2)

Automotive Terminals(142)

Insertion & Extraction Tools(6)

Other Automotive Connector Accessories(9)

Customers Also Bought

TE Part #1586019-4  
4P RCPT VAL-U-LOK V0

TE Part #1622713-1  
LR2 1% 220R

TE Part #1-1718646-1  
MCON, CONNECTOR HOUSING

TE Part #1718762-1  
MCON, RECEPTACLE AND TAB





TE Part #1326030-8  
1.5/2.8 CONNECTOR SYSTEM, RECPT AND TAB

TE Part #T4151410004-002  
M12 A-CODE FEMALE R/A SINGLE ENDED CABL

TE Part #1-1414549-0  
V23134Z1027-EV-CBOX

TE Part #1-2500035-1  
SRC Male Conduit Cover

TE Part #1394416-1  
TIMER, CONNECTOR HOUSING

Documents

Product Drawings

070 MULTI LOCK PLUG HSG 20P

Japanese

CAD Files

Customer View Model

ENG\_CVM\_174952-7\_E1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_174952-7\_E1.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_174952-7\_E1.2d\_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MULTILOCK Connector System

English

Product Specifications

Product Specification

Japanese

Product Specification

Japanese

174952-7

Multilock Connector System, Housing for Female Terminals, Wire-to-Wire, 20  
Position, 5.5mm / 3.5mm [.217in / .138in] Centerline, Yellow, Signal

