



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Power Positions	0
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Contact Features

Contact Layout	Inline
----------------	--------



Contact Retention Within Housing	Without
Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Polarization
Mating Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Mating Retention Type	Latch

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Black
Housing Material	PA 6/6

Dimensions

Height	10.05 mm
Length	9.06 mm

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Other

--	--



For Use With	Cap Housing
--------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 175156-2
U/P REC CONT L/P



TE Part # 175155-1
UNIV POWER REC CONT L/P





TE Part # 178495-1
UP 3.96 2P DIP HDR NAT






TE Part # 176282-4
AMP UNIVERSAL POWER CAP 2P



 TE Part # 176282-1 AMP UNIVERSAL POWER CAP 2P	 TE Part # 175152-1 UNIVERSAL POWER REC	 TE Part # 175152-2 AMP UNIVE. POWER CONN REC CONT	 TE Part # 175151-2 AMP UNIVE. POWER CONN REC CONT
 TE Part # 175155-2 U/P REC CONT L/P	 TE Part # 175156-1 UNIV POWER REC CONT L/P	 TE Part # 176282-2 AMP UNIVERSAL POWER CAP 2P	 TE Part # 178495-9 UP 3.96 2P DIP HDR BLACK
 TE Part # 176292-1 UNIV POWER CAP HSG 2P P/MOUNT	 TE Part # 9-176975-1 AMP UNIVERSAL POWER PLG 2P PCB	 TE Part # 176282-6 AMP UNIVERSAL POWER CAP 2P	 TE Part # 175151-1 AMP UNIVERSAL POWER REC CONT.
 TE Part # 175151-5 AMP UNIVERSAL POWER CONN.REC C	 TE Part # 1-176975-1 AMP UNIVERSAL POWER PLG 2P PCB	 TE Part # 1-176975-9 UNIV POWER HDR ASSY 2P BLACK	 TE Part # 176975-2 UNIV POWER HDR ASSY 2P RED

Also in the Series | AMP Universal Power

 Connector Contacts(1)	 Insertion & Extraction Tools(1)	 Power Contacts(21)	 Rectangular Power Connectors(171)
--	---	---	--

Customers Also Bought



TE Part #1-1376389-2
STD Temp Power Key Plug

TE Part #1-1123724-4
3.96EP HDR ASSY 4(7)P NATURAL

TE Part #1554296-1
STD Temp Sig GRACE INERTIA Plug

TE Part #1-172131-1
FF 250 REC HSG 3P NYLON NAT

TE Part #1-1473058-3
EP CONN HDR 3/6P

TE Part #1-2314812-2
12P,2MM,B-B,REC,DRVT,2,0,0.1AU,TB,W/CAP

TE Part #YDIV44E15-35SNC001
RECP ASSY

TE Part #1-172127-1
FF 250 REC HSG 1P NYLON NAT

TE Part #1-172128-1
FF 250 PLUG HSG 1P NYLON NAT

Documents

Product Drawings

AMP UNIVERSAL POWER PLUG 2P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_176271-9_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_176271-9_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_176271-9_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



[Crimping of Universal Power Contact](#)

English

[Product Specification](#)

Japanese

[AMP Universal Power Connector](#)

Japanese

[Product Environmental Compliance](#)

[MD_176271-9_07092014114_dmtec](#)

English

[MD_176271-9_07092014114_dmtec](#)

English

[Instruction Sheets](#)

[AMP UNIVERSAL POWER CONNECTOR SERIES](#)

English

[Instruction Sheet \(non U.S.\)](#)

English

[Agency Approvals](#)

[UL Report](#)

English