




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board, Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **7.92 mm [.312 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Power Positions	0
Number of Signal Positions	0
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
Insulation Resistance	1000 MΩ

Contact Features



Contact Layout	Inline
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	7 A
Contact Retention Within Housing	Without
Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Polarization
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Mating Retention Type	Latch

Housing Features

Centerline (Pitch)	7.92 mm[.312 in]
Housing Color	Natural
Housing Material	Nylon 6/6

Dimensions

Height	7 mm[.28 in]
Length	19.3 mm[.76 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

--	--



Packaging Method	Bag
Packaging Quantity	1000

Other

For Use With	Header Assembly
--------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 175156-2
U/P REC CONT L/P



TE Part # 176976-1
AMP UNIVERSAL POWER PLG 3C PCB



TE Part # 175155-1
UNIV POWER REC CONT L/P





TE Part # 2-178496-1
UNIV. POWER HDR H ASSY 2P NAT.



 TE Part # 175152-1 UNIVERSAL POWER REC	 TE Part # 175152-2 AMP UNIVE. POWER CONN REC CONT	 TE Part # 175151-2 AMP UNIVE. POWER CONN REC CONT	 TE Part # 175155-2 U/P REC CONT L/P
 TE Part # 175156-1 UNIV POWER REC CONT L/P	 TE Part # 6-176976-1 AMP UNIVERSAL POWER PLG 2C PCB	 TE Part # 3-176976-1 AMP UNIVERSAL POWER PLG 2C PCB	 TE Part # 176976-4 UNIV POWER HDR ASSY 3P YELLOW
 TE Part # 2-178496-4 UNIV. POWER HDR H ASSY 2P YEL.	 TE Part # 3-176976-6 UNIV POWER HDR ASSY 3P BLUE	 TE Part # 3-176976-2 UNIV POWER HDR ASSY 3P RED	 TE Part # 175151-1 AMP UNIVERSAL POWER REC CONT.
 TE Part # 3-176976-4 UNIV. POWER HDR ASSY 3P	 TE Part # 175151-5 AMP UNIVERSAL POWER CONN. REC C	 TE Part # 3-176976-9 UNIV POWER HDR ASSY 3P BLACK	 TE Part # 175151-4 UNIVESAL POWER REC CONT #26-22

Also in the Series | AMP Universal Power

 Connector Contacts(1)	 Insertion & Extraction Tools(1)	 Power Contacts(21)	 Rectangular Power Connectors(171)
--	---	---	--

Customers Also Bought



TE Part #1376477-6
2.5MM PITCH SIGNAL MATE CONN




TE Part #170120-1
MATE-N-LOK SOCKET 2




TE Part #170092-4
FF 250 REC 18-14AWG TPBR
REREELING



TE Part #1-353293-2
MINI CT MT REC ASSY 12P GRAY



TE Part #170043-2
110 FASTON,REC.,24-20 AWG,TPBR



TE Part #170183-2
250 FASTON,REC.,22-18 AWG,TPBR



TE Part #42563-2
FASTON 250 FLAG REC 12-10 AWG
TPBR



TE Part #1318125-2
DYNAMIC 2000 HDR ASSY



TE Part #1-1747145-5
DZ5200 H-HDR ASSY 5P 5.08MM
PITCH



TE Part #1-1747147-5
DZ5200 V-REC ASSY 5P 5.08MM PITCH

Documents

Product Drawings

U/POWER PLUG HSG 2P 7.92M/M

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_178125-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_178125-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_178125-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



[Crimping of Universal Power Contact](#)

English

[Product Specification](#)

Japanese

[AMP Universal Power Connector](#)

Japanese

[Product Environmental Compliance](#)

[MD_178125-1_051620181230_dmtec](#)

English

[MD_178125-1_051620181230_dmtec](#)

English

[Instruction Sheets](#)

[AMP UNIVERSAL POWER CONNECTOR SERIES](#)

English

[Instruction Sheet \(non U.S.\)](#)

English

[Agency Approvals](#)

[UL Report](#)

English