



MQS

TE Internal #: 1379219-1
MQS, Housing for Female Terminals, Wire-to-Wire, 12 Position, 2.54 mm [.1in] Centerline, Black, Signal
[View on TE.com >](#)

Connectors > Automotive Connectors > Connector Housings > MQS, CONNECTOR HOUSING



Connector & Housing Type: **Housing for Female Terminals**
Mating Tab Width: **.63 mm [.025 in]**
Connector System: **Wire-to-Wire**
Number of Positions: **12**
Centerline (Pitch): **2.54 mm [.1 in]**

[All MQS, CONNECTOR HOUSING \(575\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	12
Number of Rows	2

Electrical Characteristics

Operating Voltage	16 VDC
Nominal Voltage Architecture	12 V

Body Features

Cable Exit Angle	180°
Body Material	PBT GF
Primary Product Color	Black

Contact Features

Mating Tab Width	.63 mm[.025 in]
------------------	-----------------



Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Width	16.8 mm[.661 in]
Product Length	20.4 mm[.803 in]
Product Height	7.8 mm[.307 in]
Row-to-Row Spacing	5.5 mm, 7.6 mm[.217 in][.299 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C [158 °F][167 °F][176 °F][185 °F][194 °F][212 °F]
Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-SIGH262 SIGNAL HEADER	 TE Part # CAT-M8793-T273 MQS, RECEPTACLE AND TAB	 TE Part # 1379096-2 COV+LEV MQS 12W 90DEG BLU	 TE Part # 1379096-1 COV+LEV MQS 12W 90DEG BRO
 TE Part # 1379096-3 COV+LEV MQS 12W 90DEG BLK	 TE Part # 1379095-1 COV+LEV MQS 12W 0DEG BROW	 TE Part # 1379095-3 COV+LEV MQS 12W 0DEG BLAC	 TE Part # 1379095-2 COV+LEV MQS 12W 0DEG BLUE

Also in the Series | MQS



Automotive Connector Caps & Covers (133)	Automotive Connector EMC Shielding (2)	Automotive Connector Locks & Position Assurance(29)	Automotive Headers(207)
Automotive Housings(498)	Automotive Seals & Cavity Plugs(26)	Automotive Terminals(98)	Data Connectivity Headers(1)
Insertion & Extraction Tools(42)	Other Automotive Connector Accessories(13)		

Customers Also Bought

TE Part #1379029-5 MQS, CONNECTOR HOUSING	TE Part #1241404-1 AMP MCP, RECEPTACLE AND TAB	TE Part #968678-2 MQS, RECEPTACLE AND TAB	TE Part #1379096-2 COV+LEV MQS 12W 90DEG BLU
TE Part #1379096-1 COV+LEV MQS 12W 90DEG BRO	TE Part #1379096-3 COV+LEV MQS 12W 90DEG BLK	TE Part #1379095-1 COV+LEV MQS 12W 0DEG BROW	TE Part #1379095-3 COV+LEV MQS 12W 0DEG BLAC



Documents

Product Drawings

12POS MQS REC

English

CAD Files

Customer View Model

ENG_CVM_1379219-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_1379219-1_B.3d_stp.zip

English

Customer View Model

ENG_CVM_1379219-1_B.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Micro Quadlok Interconnection System (MQS)

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Recommandations Generales D'Utilisation - 12 Voies MQS

English

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

French

1379219-1

MQS, Housing for Female Terminals, Wire-to-Wire, 12 Position, 2.54mm [.1in]
Centerline, Black, Signal

