




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Quick Disconnect Mating Tab Width: **6.35 mm [.25 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Low
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Pre-Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Dimple
Extraction Force	5.9 – 29.4 Newton
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.21 – 3.4 mm[.087 – .134 in]
Overall Length	21.2 mm[.834 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	.82 – 2.08 mm²
Quick Disconnect Mating Tab Width	6.35 mm[.25 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Rating	Listed
-----------	--------

Packaging Features

Packaging Quantity	4500
Quick Disconnect Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 179970-4 PL EXII 250 REC HSG 1P NYLON YELLOW	 TE Part # 179970-1 250 HSG. PL EX REC.	 TE Part # 179970-9 PL EXII 250 REC HSG 1P NYLON BLACK	 TE Part # 179970-2 PL EXII 250 REC HSG 1P NYLON RED
 TE Part # 179970-6 PL EXII 250 REC HSG 1P NYLON BLUE	 TE Part # 1318954-1 250 HSG. PL EX REC. NAT	 TE Part # 1939581-1 250 HSG. PL EX REC. 15mm 2P NAT	 TE Part # 1-1318954-1 PL EXII 250 REC HSG 1P NYLON NAT
 TE Part # 1-1318954-6 PL EXII 250 REC HSG 1P NYLON BLUE	 TE Part # 2-2150057-2 OCEAN_2.0_APPLICATOR-E-110F180F	 TE Part # 2150057-2 OCEAN_2.0_APPLICATOR-E-110F180F	 TE Part # 7-2150057-2 OCEAN_2.0_APPLICATOR-E-110F180F



TE Part # 7-2150057-7
OCEAN_2.0_SPARE_PART_KIT-110F180F

Also in the Series | Positive Lock 250



Automotive Terminals(1)




Crimp Terminal Housings(203)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(6)




Quick Disconnects(189)


Customers Also Bought



TE Part #917765-1
Signal Double Lock Tab



TE Part #1-176497-1
250 HSG. PL EX FLAG REC. NAT



TE Part #173974-1
187 HSG. PL MKII REC. NAT



TE Part #170213-2
250 FASTON,REC.,18-14 AWG,TPBR



TE Part #1-281839-2
HE13/HE14 Crimp Housings



TE Part #1747047-1
Glow Wire GRACE INERTIA Plug



TE Part #1746971-1
GRACE INERTIA Receptacle



TE Part #1-176497-7
PL EX SLEEVE 250 FLAG RED 6/6 NYLON



Documents

Product Drawings

250 PL EX REC. 18-14AWG PTBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_179974-1_J1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_179974-1_J1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_179974-1_J1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_179974-1_05312018234_dmtec

English

MD_179974-1_05312018234_dmtec

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

POSITIVE LOCK EX-II CONNECTORS, INSTRUCTION SHEET

Japanese

Agency Approvals

UL



English