




FPC

TE Internal #: 1-84534-2
FPC Connectors, Flex-to-Board, 12 Position, 1.25mm [.049in]
Centerline, Non-ZIF, Vertical, Through Hole - Solder, Connector
Height 7.8 mm [.307 in]

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors > 1.25mm FPC Connectors



Connector System: **Flex-to-Board**
Number of Positions: **12**
Centerline (Pitch): **1.25 mm [.049 in]**
Insertion Force Type: **Non-ZIF**
PCB Mount Orientation: **Vertical**

[All 1.25mm FPC Connectors \(65\)](#)

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector Product Type	Connector Assembly
Connector System	Flex-to-Board
Insertion Force Type	Non-ZIF
Sealable	No
Connector & Contact Terminates To	Flexible Printed Circuit (FPC)

Configuration Features

Compatible With Wire & Cable Type	FFC, FPC
Number of Rows	1
Number of Positions	12
PCB Mount Orientation	Vertical

Electrical Characteristics

--	--



Operating Voltage	50 VAC
-------------------	--------

Contact Features

Contact Layout	Staggered Type A
PCB Contact Termination Area Plating Material Thickness	.8 μm[31.49 μin]
Contact Type	Socket
Contact Mating Area Plating Material Thickness	.8 μm[31.49 μin]
PCB Contact Termination Area Plating Material Finish	Bright
Contact Shape & Form	Single Beam
Contact Mating Area Plating Material Finish	Bright
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	1 A

Termination Features

Termination Post & Tail Length	3.2 mm[.126 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	With
PCB Mount Retention Type	Kinked Solder Tails
PCB Mount Alignment	With
PCB Mount Retention	With
Connector Mounting Type	Board Mount

Housing Features

Housing Material	PBT GF
Housing Color	White
Centerline (Pitch)	1.25 mm[.049 in]

Dimensions

Connector Length	18.75 mm[.738 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	7.8 mm[.307 in]
Connector Width	4.8 mm[.189 in]
Accepts Flex Cable Thickness	.3 mm[.012 in]



Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
-----------------------------	---

Operation/Application

Circuit Application	Signal
---------------------	--------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Packaging Features

Packaging Quantity	170
Packaging Method	Box & Tray, Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 487576-4
12 ZIF LINE 50 ASSY

TE Part # CAT-F839-C76264125
1.25mm FPC Connectors

TE Part # 487925-9
12 ZIF LINE ASSY .100C/L

Customers Also Bought

TE Part #1676323-2
RN 0805 3K09 0.1% 10PPM 1KRL

TE Part #1-84533-2
1.25mm FPC Connectors

TE Part #1622402-1
LR1 1% 261R

TE Part #NB-PTCO-193
RTD Platinum Thin Film Element

TE Part #1461247-1
STD OEG Miniature PCB OJ/OJE Pow Relays

TE Part #1735284-4
SATA BACKPLANE RECEPTACLE, VERTICAL, SMT

TE Part #1-84984-4
1mm FFC DIP V ASSY 14P TUBE

TE Part #1-84984-2
1mm FFC DIP V ASSY 12P TUBE

TE Part #1622262-1
LR0204 1% 620K

TE Part #1622281-1
LR0204 1% 820K

Documents

Product Drawings

1.25MM FFC POST PLATED V 12P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-84534-2_E.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-84534-2_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-84534-2_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773959-6-flexible-printed-circuit-con](#)

English

FPC Connector Family

English

[5-1773461-0_Standard_FPC_Connector_Quick_Reference_Guide](#)

English

[1-1773959-7-FPC-Connectors-CN](#)

Product Specifications

[Product Specification](#)

English