



Connectors > Power Connectors > Circular Power > Circular Power Connectors > CPC SERIES 1



Connector Product Type: **Housing**  
Operating Voltage: **600 VDC**  
Connector System: **Wire-to-Wire**  
Number of Positions: **9**  
Sealable: **No**

[All CPC SERIES 1 \(57\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	Without
Number of Positions	9
Number of Power Positions	0
Keying	A
Number of Signal Positions	9

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Reverse Gender	Yes
Contact Type	Socket



Contact Protection	With
--------------------	------

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
Screw & Hole Thread Size	15/16-20 UNEF-2A
Connector Mounting Type	Panel Mount
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	With
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	Nylon, Thermoplastic
Circular Connector Shell Size	17

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
VDE Tested	Yes

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant




China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-AM71-C83998P  
CPC ACCESSORIES




TE Part # CAT-AM71-C83998J  
CPC SERIES 1




TE Part # CAT-AM71-C83998B  
CPC CABLE CLAMPS




TE Part # 207241-1  
CABLE BOOT,SZ 17,CPC




TE Part # 207387-1  
CABLE GRIP,SZ 17,CPC



TE Part # 207387-2  
CABLE GRIP,SZ 17,CPC



TE Part # 2387122-2  
PLUG CONN CA,SP,SER 1,SZ 17-9,L 1M




TE Part # 2387122-1  
PLUG CONN CA,SP,SER 1,SZ 17-9,L 0.5M






TE Part # 2387122-3  
PLUG CONN CA,SP,SER 1,SZ 17-9,L  
2M


Also in the Series | AMP CPC




Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)




Circular Connector Caps & Covers(16)




Circular Connector Hardware(3)




Circular Connector Keying Plugs(2)




Circular Connector Seals(36)




Circular Power Connectors(513)




Insertion & Extraction Tools(1)



Power Contacts(5)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #206044-1  
CPC SERIES 6



TE Part #205204-4  
D-Sub Crimp: Plug, Signal, 9 Posn, Pin  
Size 20, Shell Size 1



TE Part #1-66105-9  
TYPE III CONTACTS LP




TE Part #205205-2  
D-Sub Crimp Recpt Signal 15 Posn,  
Socket Size 20, Shell Size 2





TE Part #66506-9  
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20



TE Part #200821-1  
CMNL KEYING PLUG



TE Part #206043-1  
CPC SERIES 1



TE Part #206036-1  
RECEPT,SZ 17-16 CPC

Documents

Product Drawings

17-9 CPC RECEPT REV SEX

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_211769-1\_AE.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_211769-1\_AE.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_211769-1\_AE.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD\_211769-1\_12102013639\_dmtec

English

MD\_211769-1\_12102013639\_dmtec

English

Agency Approvals

UL Report

English