



Connectors > Automotive Connectors > Connector Housings > SUPERSEAL 1.0 HOUSINGS



Connector & Housing Type: **Housing for Female Terminals**

Mating Pin Diameter: **1 mm [.039 in]**

Connector System: **Wire-to-Board, Wire-to-Device**

Number of Positions: **34**

Centerline (Pitch): **3 mm [.118 in]**

[All SUPERSEAL 1.0 HOUSINGS \(10\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Board, Wire-to-Device
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	34
Number of Rows	4

Electrical Characteristics

Operating Voltage	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 80 V, 90 V, 125 V, 240 V

Body Features



Cable Exit Angle	180°
Body Material	PBT GF
Primary Product Color	Black

Contact Features

Mating Pin Diameter	1 mm[.039 in]
---------------------	---------------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	3 mm[.118 in]
--------------------	---------------

Dimensions

Product Width	38.2 mm[1.504 in]
Product Length	32.15 mm[1.266 in]
Product Height	38 mm[1.496 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-40 – 125 °C, -40 – 125 °C[-40 – 257 °F][-40 – 257 °F]

Industry Standards

Degree of Protection	JIS D0203
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	500
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-SU763-H342
SUPERSEAL 1.0 HEADERS

TE Part # CAT-SU763-T273
SUPERSEAL 1.0 CONTACTS

Also in the Series | SUPERSEAL 1.0mm



Automotive Headers(24)



Automotive Housings(11)




Automotive Seals & Cavity Plugs(1)



Automotive Terminals(6)

Customers Also Bought



TE Part #106455-3
FF 110 PLUG HSG 8P.



TE Part #1456471-2
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #1473416-1
SUPERSEAL 1.0 HOUSINGS



TE Part #1418893-1
TIMER, CONNECTOR HOUSING



TE Part #W25B-P012
DEUTSCH DT WEDGELOCKS




TE Part #1-968855-2
AMP MCP, RECEPTACLE AND TAB



TE Part #1376886-1
3900281-442=S/S PLUG ASSY 44P



TE Part #1-1414122-0
V23136J1004X050-EV-CBOX



TE Part #100132-1
CAVITY PLUG

Documents

Product Drawings

34POS,SUPERSEAL,REC HSG ASSY,SLD,COD 1

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1437285-3_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-1437285-3_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1437285-3_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

Product Specifications

[Receptacle Contact, Super Seal Connector](#)

Japanese

[Application Specification](#)

Japanese

[Super Seal Connector](#)

Japanese

[Application Specification](#)

Japanese

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[SUPER SEAL CONNECTOR PLUG HOUSING CONNECTOR](#)

English