




Terminals & Splices > PCB Terminals



Terminal & Splice Type: **Tab**

PCB Terminal Terminal Type: **Tab**

PCB Terminal PCB Thickness (Recommended): **1.57 mm [.062 in]**

PCB Terminal Mating Tab Width: **6.35 mm [.25 in]**

PCB Terminal Mating Tab Thickness: **.8 mm [.031 in]**

Features

Product Type Features

FASTON	Yes
Terminates To	Printed Circuit Board

Configuration Features

Connection Capacity	Single
Stud Hole	No
Terminal Angle	Straight

Body Features

Plating Thickness	3.81 μm[100 μin]
PCB Terminal Plating Material	Tin

Contact Features

Contact Plating Material	Tin
Terminal & Splice Type	Tab
PCB Terminal Terminal Type	Tab
Underplating Material	Copper



Terminal Size	6.35
PCB Terminal Terminal Orientation	Straight

Termination Features

PCB Terminal Termination Method	Through Hole - Solder
---------------------------------	-----------------------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

PCB Terminal PCB Thickness (Recommended)	1.57 mm[.062 in]
PCB Terminal Mating Tab Width	6.35 mm[.25 in]
PCB Terminal Mating Tab Thickness	.8 mm[.031 in]
PCB Hole Diameter	1.4 mm[.055 in]
Height Above PC Board	10.21 mm[.402 in]
Receptacle Terminal Stock Thickness	.8 mm[.031 in]
Extension Below Board	3.81 mm[.15 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

Packaging Quantity	500
PCB Terminal Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free







Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1217169-1 250 FASTON,PCB TAB,TCBR	 TE Part # 1217167-1 250 FASTON,PCB TAB,TCBR	 TE Part # 1217156-1 187 FASTON,PCB TAB,TNBR	 TE Part # 1742803-1 FASTON 312 PCB TAB TPBR
 TE Part # 62747-1 FASTON 187 TAB STAKE TPBR	 TE Part # 63900-1 FASTON 250 PCB TAB TPBR	 TE Part # 60284-2 FASTON .205 (5.21 MM) TAB TPCUBR	 TE Part # 1742686-1 250 FASTON,PCB TAB,TCBR
 TE Part # 1217754-1 250 FASTON,FLAG,PCB TAB,TNBR	 TE Part # 63849-1 FASTON 250 PCB TAB TPBR	 TE Part # 1-725996-2 110 FASTON,FLAG,PCB TAB,TPBR	 TE Part # 62262-1 FASTON 250 TAB TPBR



TE Part # 62705-1
FASTON 187 DUAL TAB PTPBR

TE Part # 1-1217056-0
250 FASTON,PCB TAB,TPBR

TE Part # 1217421-1
250 FASTON,PCB TAB,TNBR

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(143)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(144)

Quick Disconnects(466)

Splices(4)

Customers Also Bought

TE Part #1318127-1
DYNAMIC 2000 HDR ASSY

TE Part #1-770849-0
3.96mm Wire-to-board housing:
receptacle, with mating alignment, SL
156

TE Part #1-1969442-1
EP 2.5 TPA Housing, 11 Pos


TE Part #1052528-1
2052 1215 02,SMA FM JACK RECPT

TE Part #1052986-1
2054 1241 02

TE Part #1376109-1
TH/.025 CONNECTOR SYSTEM,
RECPT AND TAB

TE Part #1-215915-0
AMP-LATCH 15.2 HIGH TAPE

TE Part #1-640445-0
10P MTA156 HDR ASSY FL/STR SN



Documents

Product Drawings

250 FASTON,PCB TAB,TCBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1742188-1_C_c-1742188-1-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1742188-1_C_c-1742188-1-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1742188-1_C_c-1742188-1-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON PCB Tabs and Receptacles

English

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English