



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Fixed In Tool**
Specification Type: **TE Product Specification (114-)**
Certification: **Cannot be Certified**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
Certification	Cannot be Certified
Power Type	Manual
Tool Type	Straight Action Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1903118-2 DYNAMIC D1000 TAB CONT AU (2L) L /P	 TE Part # 1827589-2 DYNAMIC D1000 REC CONT 2L GOLD	 TE Part # 1903114-2 DYNAMIC D1000 TAB CONT AU (2L) REEL	 TE Part # 1903122-1 DYNAMIC D1000 TAB CONT TIN (2L) REEL
 TE Part # 1827572-2 DYNAMIC D1000 REC CONT 2L GOLD FORM	 TE Part # 1903126-1 DYNAMIC D1000 TAB CONT TIN (2L) L /P	 TE Part # 1871745-1 DYNAMIC D1000 REC CONT 2L PRE TIN L/P	

Customers Also Bought

 TE Part #1-1827691-2 DYNATAP 3200 TAP ASSY 24P	 TE Part #1903126-1 DYNAMIC D1000 TAB CONT TIN (2L) L /P	 TE Part #6609069-7 CORCOM FC SERIES SINGLE PHASE FILTERS	 TE Part #1-2040444-1 DYNAMIC 1500T TAB HSG 3PX F/H
---	--	---	---



TE Part #5145300-3
SMT CARD RCPT,8 POS, W/ COVER

TE Part #2255140-1
MINI SAHT D1000-M

TE Part #880683-1
.250 SERIES FASTON

TE Part #9-1579007-6
EXTRACTION TOOL

TE Part #2255141-1
MINI SAHT D1000-L

TE Part #2836347-1
OCEAN-2.0-APPLICATOR-S-060F158O

Documents

Datasheets & Catalog Pages

CERTI-CRIMP II-Premium-August-1-1773864-7

English

1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English