




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Number of Positions: **3**
Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
Insulation Resistance	1000 MΩ

Contact Features

Contact Layout	Inline
Contact Base Material	Copper Alloy



Contact Current Rating (Max)	7 A
Contact Retention Within Housing	Without
Contact Type	Tab

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Mating Alignment Type	Polarization
Mating Alignment	With
Panel Mount Feature	With
PCB Mount Retention	Without
Connector Mounting Type	Panel Mount
Mating Retention	With
Mating Retention Type	Latch

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Yellow
Housing Material	Nylon 6/6

Dimensions

Height	8.9 mm[.35 in]
Length	29 mm[1.14 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Bag
Packaging Quantity	500



Other

For Use With	Plug Housing
--------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 175153-1
UNIV POWER TAB CONT L/P



TE Part # 176272-1
AMP UNIVERSAL POWER PLUG 3P






TE Part # 175149-2
AMP UNIVE. POWER CONN TAB CONT




TE Part # 175150-2
AMP UNIVE. POWER CONN TAB CONT



 TE Part # 175153-2 U/P TAB CONT L/P	 TE Part # 175154-2 U/P TAB CONT L/P	 TE Part # 176272-2 AMP UNIVERSAL POWER PLUG 3P	 TE Part # 176272-4 AMP UNIVERSAL POWER PLUG 3P
 TE Part # 175149-1 UNIVERSAL POWER CONN TAB	 TE Part # 175150-1 UNIVERSAL POWER CONN TAB	 TE Part # 175154-1 UNIV POWER TAB CONT L/P	 TE Part # 176272-9 AMP UNIVERSAL POWER PLUG 3P
 TE Part # 175149-3 AMP UNIVERSAL POWER CONN.TAB C	 TE Part # 176272-6 AMP UNIVERSAL POWER PLUG 3P		

Also in the Series | AMP Universal Power

 Connector Contacts(1)	 Insertion & Extraction Tools(1)	 Power Contacts(21)	 Rectangular Power Connectors(171)
--	---	---	--

Customers Also Bought


 TE Part #1558665-6 PCB Power Relay: 30 amp, Monostable DC	 TE Part #1-2176414-1 7W STD M/OX 5% 51R	 TE Part #1565088-1 STD Temp GRACE INERTIA Cap	 TE Part #1463696-5 CRIMPER,WIRE FOR HI-CURRENT M
--	---	--	---



TE Part #1-409414-9
CRIMPER WIRE



TE Part #1-722979-0
WIRE, CRIMPER FOR MINI APLL F



TE Part #1463047-4
ANVIL



TE Part #1463264-2
CRIMPER, WIRE



TE Part #914541-1
CRIMPER, WIRE

Documents

Product Drawings

UNIV POWER CAP HSG 3P P/MOUNT

English

CAD Files

3D PDF

3D

3D PDF

English

Customer View Model

ENG_CVM_176293-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_176293-4_B.3d_stp.zip

English

Customer View Model

ENG_CVM_176293-4_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_176293-4_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_176293-4_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_176293-4_G.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese

AMP Universal Power Connector

Japanese

Instruction Sheets

AMP UNIVERSAL POWER CONNECTOR SERIES

English

Instruction Sheet (non U.S.)

English

Agency Approvals

UL Report

English