



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Receptacle**
Housing Type: **Receptacle**
Number of Crimp Terminal Housing Positions: **2**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Product Type	Terminal Housing
Housing Type	Receptacle
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	2
--	---

Body Features

Crimp Terminal Housing Housing Color	Black
Crimp Terminal Housing Mating Retention	Without
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Receptacle
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)
---------------------------------------	----------------------------

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Crimp Terminal Housing Centerline	7.4 mm[.291 in]
-----------------------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

Crimp Terminal Housing UL Flammability Rating	UL 94V-0
---	----------

Packaging Features

Crimp Terminal Housing Packaging Method	Carton
---	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability













Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 926526-1 PL MKI 250 REC HSG 5P NYLON BLACK</p>	 <p>TE Part # 926523-1 3P.POS.LOCK HSG</p>	 <p>TE Part # 926319-1 PL 250 REC HSG 2P NYLON BLACK</p>	 <p>TE Part # 927076-1 PL HOUSING 0.6 PA 6.6 + PE-GF13 BLACK</p>
 <p>TE Part # 926521-2 PL 250 REC HSG 2P NYLON BLACK</p>	 <p>TE Part # 926522-2 PL 250 REC HSG 2P NYLON NAT</p>	 <p>TE Part # 926522-1 PL 250 REC HSG 2P NYLON BLACK</p>	 <p>TE Part # 953043-1 PL LOCKING LEVER 3P HOUSING PA6.6 NOIR</p>
 <p>TE Part # 1-2133341-2 250 HSG. PL MKI REC. NAT</p>	 <p>TE Part # 1-926522-2 PL 250 REC HSG 2P NYLON NAT</p>	 <p>TE Part # 1-2133341-1 PL MK1 RECEPTACLE NATURAL 6.6 PA</p>	 <p>TE Part # 100100-1 2 POS POSITIVE LOCK (PL) HOUSING</p>
 <p>TE Part # 926524-1 PL 2P HOUSING PA6.6 ZYTEL 101 BLACK</p>			

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(203)



Insertion & Extraction Tools(3)




Insulation Boots & Sleeves(6)



Quick Disconnects(189)

Customers Also Bought



TE Part #142680-1
PL MK III 2 POS HOUSING BROEN
RAL 8016



TE Part #1-1670919-1
MCON, CONNECTOR HOUSING



TE Part #1452299-1
AMP MCP, UNSEALED CONNECTOR
HOUSING



TE Part #1-968326-1
MQS, CONNECTOR HOUSING



TE Part #1473140-1
SQUIB 11DIA MK-2 LOCKING BUTTO



TE Part #965412-1
MQS GRIFFSCHALE 6P



TE Part #1393429-3
V23540M5302Y 22=2P BUCHSENGEH.

Documents

Product Drawings

PL 250 REC HSG 2P NYLON BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-926522-1_S.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-926522-1_S.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-926522-1_S.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[UL Report](#)

English