



Connectors > Automotive Connectors > Connector Housings > HEAVY DUTY SEALED CONNECTOR HOUSINGS



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **1.5 mm, 2.8 mm** [.059 in, .11 in]

Connector System: **Wire-to-Wire**

Number of Positions: **7**

Centerline (Pitch): **4 mm, 6 mm** [.157 in, .236 in]

[All HEAVY DUTY SEALED CONNECTOR HOUSINGS \(186\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	Yes
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	7
Number of Rows	2

Electrical Characteristics

Operating Voltage	60 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 60 V

Body Features

Cable Exit Angle	Other
Body Material	PBT GF
Primary Product Color	Black

Contact Features



Mating Tab Width	1.5 mm, 2.8 mm[.059 in][.11 in]
------------------	---------------------------------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	4 mm, 6 mm[.157 in][.236 in]
--------------------	------------------------------

Dimensions

Product Width	25.7 mm[1.012 in]
Product Length	44 mm[1.732 in]
Product Height	31.25 mm[1.23 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	380
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-H3399-C1748
HEAVY DUTY CONNECTORS
PROTECTION CAPS




TE Part # CAT-H3399-B128
HEAVY DUTY SEALED CONNECTOR
BACKSHELLS




TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB




TE Part # CAT-H3399-CH8172
HEAVY DUTY SEALED CONNECTOR
HOUSINGS



TE Part # 964972-1
EINZELLEITERDICHTUNG



TE Part # 828905-1
SINGLE-WIRE-SEAL(5MM HOLE)



TE Part # 2-2378180-1
7POS,HYBRID,HDR ASSY,180DEG,
COD B

Also in the Series | Heavy Duty Sealed Connector Series



Automotive Connector Caps & Covers (20)



Automotive Housings(189)



Automotive Seals & Cavity Plugs(1)



Insertion & Extraction Tools(1)




Other Automotive Connector Accessories(22)

Customers Also Bought



TE Part #1393222-4
V23061A1002A302=MINISTARKSTROM



TE Part #1586314-3
VAL-U-LOK PIN PHBZ SN 24-18 LP



TE Part #1564562-2
HEAVY DUTY CONNECTORS FIXING SLIDES



TE Part #1-1564518-1
HEAVY DUTY SEALED CONNECTOR HOUSINGS



TE Part #1-962916-2
TIMER, RECEPTACLE AND TAB



TE Part #1241374-2
AMP MCP, RECEPTACLE AND TAB



TE Part #1-1718485-5
AMP MCP BACKSHELLS



TE Part #1-1823034-1
MCON, RECEPTACLE AND TAB



TE Part #W45B
DEUTSCH DT WEDGELOCKS

Documents



Product Drawings

7 POS MIXED REC HSG GR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1418480-1_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1418480-1_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1418480-1_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

HDSCS Catalog

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English