



TE Internal #: 2267087-1
Toggle Switches, Single Pole - Double Throw Configuration (Pole-Throw), Sealed Toggle Switch, Silver, Terminal Seal (Epoxy), Operating Function On On
[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Toggle Switches



Configuration (Pole-Throw): **Single Pole - Double Throw**
Sealed Toggle Switch: **Yes**
Switch Contact Plating Material: **Silver**
Process Sealed: **No**
Toggle Switch Seal Type: **Terminal Seal (Epoxy)**

Features

Product Type Features

Product Type	Switch
Sealed Toggle Switch	Yes
Toggle Switch Type	Rocker

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On

Electrical Characteristics

Toggle Switch Voltage Rating	125 VAC, 28 VDC
------------------------------	-----------------

Body Features

Toggle Switch Seal Type	Terminal Seal (Epoxy)
-------------------------	-----------------------

Contact Features

Switch Contact Plating Material	Silver
Toggle Switch Contact Current Rating	3 A

Termination Features

Termination Type	Vertical
------------------	----------

Mechanical Attachment

Toggle Switch Mounting Type	Solder lug
-----------------------------	------------

Housing Features



Process Sealed	No
----------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2267074-1
PMS9P1B05M2RE



TE Part # 2267074-3
PMS9P1B05M2QE



TE Part # 2267072-3
PMD9P1B10M6RE



TE Part # 2267074-4
PMS9P1B05M2QE



Customers Also Bought



Documents

Product Drawings

[RMS1R102M1QES](#)

English

CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_2267087-1_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_2267087-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267087-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Subminiature Switches

English