




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Wire**
Number of Positions: **8**
Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying & Polarized Rib Location	8b
Number of Positions	8
Number of Rows	1

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Locking Latch Between Cavity Number	2&3, 7&8
Strain Relief	Without



Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 6.6
Centerline (Pitch)	5 mm[.197 in]
Housing Color	Gray

Dimensions

Connector Length	40 mm[1.574 in]
Connector Height	12.2 mm[.48 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

RAST Version	None
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	1000
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 928343-2 STD-TIM GEH 2P</p>	 <p>TE Part # 2-928343-8 STD-TIMER GEH 8P</p>	 <p>TE Part # 928343-3 STD-TIMER GEH 3P</p>	 <p>TE Part # 928343-8 STD-TIMER GEH 8P</p>
 <p>TE Part # 1-928343-1 STANDARD TIMER HOUSING</p>	 <p>TE Part # 1-928343-2 STANDARD TIMER HOUSING</p>	 <p>TE Part # 2-928343-5 5P STD-TIMER GEH</p>	 <p>TE Part # 2-928343-7 7P STD-TIMER GEH</p>
 <p>TE Part # 3-928343-3 STD TIMER HOUSING 3P</p>	 <p>TE Part # 928343-9 STANDARD TIMER HOUSING</p>		



Also in the Series | RAST 5 IDC Connectors

Automotive Terminals(8)	Connector Contacts(12)	Crimp Terminal Housings(41)	Insertion & Extraction Tools(1)
Rectangular Connector Housings(1)	Standard Edge Connectors(36)	Standard Rectangular Connectors(138)	Wire-to-Board Connector Assemblies & Housings(214)
Wire-to-Board Connector Contacts(2)	Wire-to-Board Headers & Receptacles (424)		

Customers Also Bought

TE Part #2-794954-2 22P RCPT VAL-U-LOK V2	TE Part #280314 FF 250 REC HSG 6P NYLON CLEAR	TE Part #160780-4 110 FASTON,REC.,16-20 AWG,TPBR	TE Part #969191-4 TIMER, CONNECTOR HOUSING
TE Part #2112297-1 HEAVY DUTY CONNECTORS PROTECTION CAPS	TE Part #1703838-1 HEAVY DUTY CONNECTORS FIXING SLIDES	TE Part #2-1564514-1 HEAVY DUTY SEALED CONNECTOR HOUSINGS	TE Part #185636-1 PROTECT CAP 2.5MM PLUG



Documents

Product Drawings

[STD-TIMER GEH 8P](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-928343-8_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-928343-8_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-928343-8_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Agency Approvals

[VDE Certificate](#)

English