



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.65 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire/Cable Type	Regular Wire
Wire Stop	No
Insertion Force	Normal
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Electrical Characteristics

Voltage (Max)	250 V
---------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight



Contact Base Material	Phosphor Bronze
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Mating Retention Type	Locking Lance
Extraction Force	4 Newton
Locking Lance Height	1.2 mm
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.31 – 3.3 mm[.091 – .129 in]
Receptacle Terminal Stock Thickness	.25 mm[.01 in]
Overall Length	16 mm[.629 in]
Wire Size	.51 – 1.65 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	8000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-2150309-1 OCEAN_2.0_APPLICATOR-E-090F130F	 TE Part # 2-2150309-2 OCEAN_2.0_APPLICATOR-E-090F130FA	 TE Part # 2150309-1 OCEAN_2.0_APPLICATOR-E-090F130F	 TE Part # 2150309-2 OCEAN_2.0_APPLICATOR-E-090F130FA
 TE Part # 281197-5 FF 187 REC 1.0-2.5MM2 PTBR (RE REELING)	 TE Part # 281197-6 FF 187 REC 1.0-2.5MM2 PTBR	 TE Part # 7-2150309-1 OCEAN_2.0_APPLICATOR-E-090F130F	 TE Part # 7-2150309-2 OCEAN_2.0_APPLICATOR-E-090F130FA
 KIT TE Part # 7-2150309-7 OCEAN_2.0_SPARE_PART_KIT-090F130F			

Also in the Series | FASTIN-FASTON 187



Crimp Terminal Housings(8)



Insertion & Extraction Tools(1)




Quick Disconnects(21)


Customers Also Bought




TE Part #1-917542-3
DYNAMIC D-5 S/ROW HDR ASY 4P V




TE Part #962496
FF 250 TAB HSG 1P NYLON CLEAR



TE Part #174513-1
PL 187 HOUSING RECEPTACLE




TE Part #175034-1
PL 187 REC 20-14 AWG 0.30 X 14.0 SS



TE Part #1355901-1
MCP9,5 BU-GEH 1P



TE Part #1-1904045-6
V23333Z0001B046-EV-100



TE Part #1-172210-1
187 HSG. PL MKII REC. 6mm 2P NAT



TE Part #444311-1
HSG 12 POSN, FUSE C



TE Part #5-2295787-5
STD TIMER PLUG HSG 5P W/EXT. LOCKING-SP



TE Part #2-2819195-4
2 W ABS CABLE ASSY MBB 8.000

Documents

Product Drawings

FF 187 REC 0.5-1.5MM2 TPPB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_280919-4_M.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_280919-4_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_280919-4_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

[FASTIN-FASTON Connector, .187 rec. etc.](#)

Product Environmental Compliance

[MD_280919-4_07282015023_dmtec](#)

English

[MD_280919-4_07282015023_dmtec](#)

English