



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.5% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-1105851-8
RSZ.HE-HND-HVT



TE Part # 1-1105850-8
RSZ.BAS



TE Part # 1102855-7
AWZG-HE-Q5-RSZ



TE Part # 2063561-2
SDE P&S ROUND 12-14AWG DIE



Was called:
SDE PEW 12

Now renamed to:
SDE SA
(no other physical changes)

TE Part # 2063583-1
SDE HN.D HVT HE/HA 0.13-4.0mm2
ASSY



TE Part # 1-1105852-8
RSZ.C 0,14-4MM2

Also in the Series | **HDC HSB**



Insertion & Extraction Tools(2)



Rectangular Contact Inserts(8)

Customers Also Bought



TE Part #1-178802-5
DYNAMIC 3100 REC AND TAB HSG



TE Part #164531-4
D-Sub Crimp Recpt Signal 9 Posn,
Socket Size 20, Shell Size 1



TE Part #2-111196-0
40 RCPT SYSTEM 50, LEAD FREE




TE Part #2-1393225-3
RY612005



TE Part #1-338168-2
D-Sub Plug Assembly: Standard, Right
Angle, Shell Size 1, 2.74mm



TE Part #1-964296-3
TIMER, RECEPTACLE AND TAB



TE Part #946593-000
TTMS-4.8-9



TE Part #1-1102296-1
HB.16.AG-VS



Documents

Product Drawings
[HE/HA-C-BU.AU.4,0](#)

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-1105101-2_J_c-5-1105101-2-j.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1105101-2_J_c-5-1105101-2-j.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1105101-2_J_c-5-1105101-2-j.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.