




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Plug**
Connector System: **Wire-to-Board**
Number of Positions: **4**
Centerline (Pitch): **3.5 mm [.138 in]**
Number of Rows: **1**

Features

Product Type Features

Wire Protection	With
Block Type	Stacking Plug
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	4
Number of Rows	1
Wire Entry Angle	Side

Electrical Characteristics

Current Rating (Max)	11 A
Voltage Rating	300 VAC

Body Features



Interlock	Without
-----------	---------

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	11 A

Mechanical Attachment

Screwless Terminal Block	No
Mounting Angle	Right Angle
Screw Size	M2
Screw Plating Material	Nickel
Screw Material	Brass
Screw Flange	Without

Housing Features

Housing Color	Green
Housing Material	PA 66
Centerline (Pitch)	3.5 mm[.138 in]

Dimensions

Wire Size	.05 – 2 mm²
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	150
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)



Candidate List Declared Against: JAN 2021 (211)
SVHC > Threshold:
Pb (.58% in Component Part)


Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 284512-4
4 POS TERMI-BLOK HDR 900 POLAR



TE Part # 796693-4
4 POS TERMI-BLOK PLUG STACK




TE Part # 284514-4
4 POS TERMI-BLOK HDR DIR. POL.




TE Part # 1776130-4
4P TERMI-BLOK HDR,HIGH TEMP



TE Part # 1776242-4
4 POS TERMI-BLOK PLUG STACK 3,



TE Part # 284540-4
4 POS TERMI-BLOK 900 O.E. 3,5



TE Part # 3-796693-4
4 POS EUROSTYLE TB WHITE INK

Customers Also Bought






TE Part #1623795-5
Wirewound Resistor: Horizontal Mount



TE Part #1-5103308-0
A/L LOW PRO HDR 50P VERT BLACK



TE Part #120591-1
TOP LOAD BATTERY




TE Part #1546074-6
6 POS 5.08MM TERMI-BLOK TOP WI



TE Part #1-1879417-1
CPF 0603 470K 0.1% 25PPM 1K RL




TE Part #1393118-7
KUP-14DE5-24=KU



TE Part #NB-PTCO-011
RTD Platinum Thin Film Element



TE Part #1-84953-0
1MM FPC HORZ.TOP CONT.ASSY 10P



TE Part #1-284506-2
12 POS TERMI-BLOK PLUG STAC 3,



TE Part #1393130-7
PRD-7AY0-120=PRD

Documents

Product Drawings

4 POS TERMI-BLOK PLUG STACK 3,

English

CAD Files

Customer View Model

ENG_CVM_284506-4_C.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_284506-4_C.3d_igs.zip

English

Customer View Model

ENG_CVM_284506-4_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[Eurostyle Terminal Blocks Focus Product Stock List](#)

English

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

[Product Specifications](#)

[Application Specification](#)

English

[Product Environmental Compliance](#)

[Product Compliance](#)

English

[Product Compliance](#)

English