



RAST

TE Internal #: 3-1534415-2

Standard Edge Connectors, Wire-to-Board, 2 Position, 5mm [.197in]

Centerline, Insulation Displacement Crimp (IDC), 1 Row, Natural

Housing Color, PA 6

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **5 mm [.197 in]**

Termination Method to Wire & Cable: **Insulation Displacement Crimp (IDC)**

Number of Rows: **1**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Card Entry Style	Side
Number of Insulation Displacement Slots	2
Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	2
Number of Rows	1
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Right Angle

Electrical Characteristics

UL Voltage Rating	250 VAC
Operating Voltage	250 V



Body Features

Keying Between Cavity Locations	R2.5 / PRL-2-
Connector Profile	Standard

Contact Features

Contact Retention Within Housing	With
Contact Type	Socket
Contact Mating Area Plating Material Thickness	3 – 6 µm[196.849 – 787.399 µin]
Contact Mating Area Plating Material	Tin
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	CuNiSi
Contact Current Rating (Max)	6 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)
------------------------------------	-------------------------------------

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Retention	With
Mating Alignment	With
Contact Retention Type Within Housing	Locking Lance
PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	One End Open
Centerline (Pitch)	5 mm[.197 in]
Housing Color	Natural
Housing Material	PA 6

Dimensions

Connector Height	7.3 mm[.287 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]
Accepts Wire Insulation Diameter Range	2.2 mm[.087 in]
Wire Size	.35 – .5 mm²



Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Agency/Standard	UL
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Method	Tray
Packaging Quantity	3850

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1534415-3
DUOPL POW FEM CON3P

TE Part # 1534415-2
DUOPL POW FEM CON2P

TE Part # 1394918-2
DUOPLG5.0 BU-STE 2P

TE Part # 1534415-4
DUOPL POW FEM CON4P

TE Part # 1534415-5
DUOPL POW FEM CON5P

TE Part # 1534415-7
DUOPL POW FEM CON7P

TE Part # 1534415-6
DUOPL POW FEM CON6P

TE Part # 1534415-8
DUOPL POW FEM CON8P

TE Part # 2-1394918-2
DUOPLG5.0 BU-STE 2P

TE Part # 1-1394918-2
DUOPLG5.0 BU-STE 2P

TE Part # 1-1534415-2
DUOPL POW FEM CON2P

TE Part # 2-1534415-2
DUOPL POW FEM CON2P

TE Part # 2-1534415-3
DUOPL POW FEM CON3P

Customers Also Bought

TE Part #4-641237-6
Nylon Gold Plated Receptacle: 2.54 mm, No Mating Alignment, MTA 100

TE Part #1-1969590-0
HSG, REC, PANEL MOUNT, SINGLE ROW,EP2.5

TE Part #1-1744418-1
11 POS EP 2.5 HDR, GLOW WIRE

TE Part #163686-1
03P.CIS FEMALE CONN



TE Part #2-1586861-4
24P PM PLUG VAL-U-LOK PM GW

TE Part #2150038-2
OC-AT-E-FA-120F180F-001-0080

TE Part #2150425-2
OCEAN_2.0_Applicator-E-140F280FA

TE Part #2836253-1
OCEAN_2.0_Applicator-S-071F098O

TE Part #4-1415535-1
RTE43009

TE Part #CV4205-000
RNF-100-3/8-WH-STK-SH

Documents

Product Drawings

DUOPL POW FEM CON2P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1534415-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1534415-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1534415-2_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration



English

[Agency Approvals](#)

[VDE Certificate](#)

English

[VDE Certificate](#)

English