




Free Height

TE Internal #: 3-1827253-6
Free Height, PCB Mount Header, Vertical, Board-to-Board, 220
Position, .5mm [.02in] Centerline, Gold, Printed Circuit Board
[View on TE.com >](#)

Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **220**
Centerline (Pitch): **.5 mm [.02 in]**

Features

Product Type Features

Ground Component Type	Grounding Contact, Grounding Plate
PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Rows	2
Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	220
Board-to-Board Configuration	Parallel

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	200 VAC
Insulation Resistance	2 MΩ
Operating Voltage	50 VAC



Contact Features

Contact Layout	Inline
Contact Mating Area Length	1 mm, 1.3 mm
PCB Contact Termination Area Plating Material Thickness	.05 µm[1.9685 µin]
Mating Tab Width	.33 mm[.013 in]
Mating Tab Thickness	.2 mm[.008 in]
Contact Shape & Form	Square
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.2 µm[7.874 µin]
Contact Type	Pin
Contact Current Rating (Max)	.5 A

Termination Features

Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Rectangular Termination Post & Tail Width	.71 mm[.028 in]
Termination Method to Printed Circuit Board	Surface Mount

Mechanical Attachment

PCB Mount Alignment Type	Locating Posts
PCB Mount Retention Type	Solder Peg
Mating Alignment	With
Mating Alignment Type	Polarization
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	.5 mm[.02 in]
Housing Color	Black
Housing Material	High Temperature Thermoplastic

Dimensions

Connector Height	4.45 mm[.175 in]
Stack Height	5 mm, 9 mm[.354 in]



	.2 in
--	-------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
-----------------------------	---

Operation/Application

Assembly Process Feature	None
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	150
Packaging Method	Hard Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 3-6318491-6 .5FHP08H,220,S,GIG,08/Sn,HT,NSYes	 TE Part # 3-1939756-6 .5FHP08H,220,S,GIG,30/Sn,HT,NS	 TE Part # 3-6318490-6 .5FHR04H,220,S,GIG,08/Sn,HT,NSYes	 TE Part # 6-5353606-6 .5FHR04H,220,S,GIG,08/Sn,HT,SEYes
 TE Part # 3-2040713-6 .5FHP08H,220,S,GIG,30/Sn,TR,NS	 TE Part # 3-1939755-6 .5FHR04H,220,S,GIG,30/Sn,HT,NS	 TE Part # 9-1939756-6 .5FHP08H,220,S,GIG,30/Sn,HT,NS,WC	 TE Part # 3-2040714-6 .5FHR04H,220,S,GIG,30/Sn,TR,NSYes
 TE Part # 4-1827253-6 .5FHP05H,220,S,GIG,08/Sn,TR,NSYes	 TE Part # 9-1827231-6 .5FHR04H,440,B,GIG,30/Sn,HT,NS	 TE Part # 9-1827253-6 .5FHP05H,220,S,GIG,30/Sn,HT,NSYes	

Also in the Series | Free Height



Board-to-Board Headers & Receptacles(764)

Customers Also Bought



TE Part #1367073-1
SFP Connectors



TE Part #1-1469492-1
MULTIGIG RT 9MM GUIDE/ESD 0 DEG



TE Part #1410189-3
MULTIGIG RT T2 7RW H-LFT,ET2



TE Part #1-1469492-9
MULTIGIG RT 9MM GUIDE/ESD UNKE



TE Part #1410140-1
MULTIGIG RT T2 .8" BP FULL CNT



TE Part #1410187-3
MULTIGIG RT T2 7RW DC DF CT




TE Part #1-964296-3
TIMER, RECEPTACLE AND TAB



TE Part #ZPF000000000110281
732-8255-22



TE Part #1-1600636-5
MBXL PANEL MT 4P+24S+4P



TE Part #1-215307-4
2X14P HV100 REC CON. TE, 7.0MM

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1827253-6_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1827253-6_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1827253-6_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Fine Pitch Stacking Connectors - 0.5mm Free Height (FH) Connectors

English

[COM Connectors Brochure \(English\)](#)

English



Product Specifications

Application Specification

English

Product Environmental Compliance

MD_3-1827253-6_053020182159_dmtec

English

MD_3-1827253-6_053020182159_dmtec

English