



AMP

TE Internal #: 521207-1

Housing, Receptacle, Wire-to-Wire, 5 Position, 5mm [.197in]

Centerline, Crimp, 1 Row, Row-to-Row Spacing .197 in [5 mm], Blue

Housing Color

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Wire**

Number of Positions: **5**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	5
Number of Rows	1

Contact Features

Contact Layout	Inline
Contact Type	Socket
Contact Base Material	Brass

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Both Ends Closed
Housing Material	Nylon 6/66
Centerline (Pitch)	5 mm [.197 in]
Housing Color	Blue

Dimensions

Connector Length	9.2 mm [.362 in]
Connector Height	12.2 mm [.48 in]
Row-to-Row Spacing	5 mm [.197 in]

Usage Conditions

Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant








China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 521206-1 POSI-LOK HSG.250-4 POS RAST5	 TE Part # 521207-3 HSG POSI-LOCK MARK III	 TE Part # 521209-1 POSI-LOK HSG.250-7 POS RAST5	 TE Part # 521210-5 HSG,RAST 5,POSI LOCK MKIII,8P
 TE Part # 521207-4 HSG,RAST 5,POSI LOCK MKIII,5P	 TE Part # 521210-1 POSI-LOK HSG.250-8 POS RAST5	 TE Part # 521206-3 HSG,4P,POS LOCK,MKIII,250 SERI	 TE Part # 521206-6 POSI-LOK HSG.250-4 POS RAST5



TE Part # 521209-2
HSG POSI-LOCK MARK III



TE Part # 521210-3
HSG,POS-LOC,MKIII,250SERIES,6P




TE Part # 521267-1
POSI-LOK HSG.250-5 POS RAST5



TE Part # 521206-2
250 SERIES 4 POS POSILOK HSG



TE Part # 521206-4
HSG,POSI-LOCK MKIII RAST,4P



TE Part # 521206-5
HSG,RECP,POSI-LOCK MKIII,4P



TE Part # 521207-2
POSI-LOK HSG 250 5P RAST5



TE Part # 521207-5
HSG POSI-LOK 250 (05-B) RAST



TE Part # 521208-2
HOUSING POSITIVE LOCK RAST



TE Part # 521210-4
HSG,POSILOCK, MKIII, 8 POS,250

Customers Also Bought



TE Part #T4131512051-000
M12 Panel Mount Solder Cups



TE Part #1586105-3
3P RCPT VAL-U-LOK SR V2



TE Part #1-963214-1
TIMER, CONNECTOR HOUSING



TE Part #1-480699-0
02P UMNL CAP HSG NATL



TE Part #1-794606-2
MICRO MNL RPT CNT STRP 30AU LF



TE Part #1742539-3
CLUSTER BLOCK RECEPT,TPCuFeP



TE Part #1-2119784-7
CRIMPER, INSUL O PREMIUM



TE Part #1-2336231-6
Power Versa-Lock TNL CAP, 2X3 KEY A



Documents

Product Drawings

POSI-LOK HSG.250-5 POS RAST5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_521207-1_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_521207-1_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_521207-1_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English