



Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**
Operating Voltage: **600 VAC**
Contact Mating Area Plating Material: **Gold**
Wire Size: **.5 – 2 mm²**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	19 A
Contact Type	Socket
Contact Retention Within Housing	With
Mating Pin Diameter	2.13 mm[.084 in]
Contact Base Material	Brass
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Wire Contact Termination Area Plating Material Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Material	Nickel



Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Connector Mounting Type	Cable Mount (Free-Hanging)
Wire Insulation Support	Without

Dimensions

Wire Size	.5 – 2 mm²
Accepts Wire Insulation Diameter Range	3.3 – 5.08 mm[.13 – .2 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

CSA Rating	Certified
Glow Wire Rating	Standard Part - Not Glow Wire
VDE Tested	Yes
Agency/Standard	CSA
CSA File Number	LR 7189
UL Rating	Recognized
UL Flammability Rating	UL 94V-0
UL File Number	E28476

Packaging Features

Packaging Method	Reel
Packaging Quantity	1000

Other

Wire/Cable Type	Discrete Wire
Wire Type	Stranded



For Use With	Universal MATE-N-LOK Plug or Socket Housing
--------------	---

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 90547-1
ASSY PRO-CRIMPER UNIV M-N-L



TE Part # 91506-1
CCII UNML UNML II PIN SKT 16-14 ASSY



TE Part # 90547-2
PROCrimper Die AssY UNIV MNL








TE Part # 1804030-1
EXTRACTION TOOL ASSY




 TE Part # 1-480705-2 06P UNML CAP HSG RED	 TE Part # 1-480708-9 12P UMNL PLUG HSG BLK	 TE Part # 926307-3 6P UN-MNL AUFN-GEH	 TE Part # 1-480704-2 06P UMNL PLUG HSG RED
 TE Part # 926302-1 10& UNIV.M-N-L.PLUG	 TE Part # 1-350777-2 02P UMNL V0 PLUG HSG RED	 TE Part # 350783-1 12P UMNL CAP HSG	 TE Part # 1-350778-9 02P UMNL V0 CAP HSG BLACK
 TE Part # 350735-1 12P UMNL PLUG HSG	 TE Part # 926302-3 10P UN-MNL STECKGEH	 TE Part # 926308-3 8P UN-MNL AUFN-GEH	 TE Part # 1-350766-2 03P UMNL V0 PLUG HSG RED
 TE Part # 1-480701-4 03P UMNL CAP HSG YELL	 TE Part # 640585-1 06P UMNL PLUG HSG V2 NATL	 TE Part # 926308-1 8P UNIV.M-N-L.CAP	 TE Part # 926309-1 10P UNIV.M-N-L.CAP

Also in the Series | Universal MATE-N-LOK

 Circular Power Connectors(2)	 Connector Contacts(11)	 Insertion & Extraction Tools(4)	 Power Contacts(207)
---	--	--	--



Rectangular Boots & Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(725)

Customers Also Bought



TE Part #208718-1
CMC SERIES 1



TE Part #2007304-5
QSFP Heat Sink Clips



TE Part #1-480764-0
05P UMNL CAP HSG NATL




TE Part #2-1393763-3
V23100V4305C11




TE Part #206508-1
TYPE XII KEYING PLUG



TE Part #1-178298-3
DYNAMIC 3100 HDR ASSY



TE Part #111607-000
TXR21AB00-1410AI



TE Part #170333-1
PL 250 RECEPTACLE 22-18 AWG PTPBR



TE Part #9304773001
100G0111-2.00-0CK0042



TE Part #1437382-6
70=300/600V JUMPER (PKG D)

Documents



Product Drawings

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_350551-7_P.3d_igs.zip

English

Customer View Model

ENG_CVM_350551-7_P.3d_stp.zip

English

Customer View Model

ENG_CVM_350551-7_P.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_350551-7_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_350551-7_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_350551-7_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Engineering Report

English

Product Environmental Compliance

UMNL SOK 20-14 AU/BR L/P

English

UMNL SOK 20-14 AU/BR L/P

English

Instruction Sheets

Instruction Sheet (U.S.)

English