




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire/Cable Type	Regular Wire
Insertion Force	Normal
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open



Mechanical Attachment

Mating Retention Type	Locking Lance
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.16 – 3.18 mm[.081 – .125 in]
Overall Length	20.26 mm[.798 in]
Receptacle Terminal Stock Thickness	.3 mm[.012 in]
Wire Size	.32 – .82 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 4-1579007-3
EXTRACTION TOOL KIT




TE Part # 1-1579007-4
EXTRACTION TOOL



TE Part # 2217747-1
CCII FASTIN-FASTON 22-18 ASSY

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(218)



Insertion & Extraction Tools(2)




PCB Terminals(2)



Quick Disconnects(255)

Customers Also Bought



TE Part #180907-5
FF 250 REC HSG 2P NYLON BLACK




TE Part #7-1393163-6
MTMT00A0



TE Part #HDP24-24-33SN-L017
REC, 33P, BLK, N, RNG, 20, S



TE Part #81117-000
LS509-51 Liquid Level Sensor



TE Part #2820623001
44A0211-10-9




TE Part #BFC110N00000207000
923 RECEPTACLE, ANGLED



TE Part #BKA186M21480200000
923 EXTENSION, SPEEDTEC-READY



TE Part #BEA120M42000200000
923 RECEPTACLE, SPEEDTEC-READY



Documents

Product Drawings

FF 250 REC 22-18AWG TPBR LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60838-1_E_c-60838-1-e.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60838-1_E_c-60838-1-e.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60838-1_E_c-60838-1-e.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English

Product Environmental Compliance

MD_60838-1_033020181249_dmtec

English

MD_60838-1_033020181249_dmtec

English