



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**
Insertion & Extraction Tool Application: **Contact-to-Wire**

Features

Product Type Features

| | |
|---|--------------------|
| Insertion & Extraction Tool Type | Contact Extraction |
| Insertion & Extraction Tool Application | Contact-to-Wire |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Out of Scope |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|--|--|--|--|
|  <p>TE Part # CAT-M8793-T273 MQS, RECEPTACLE AND TAB</p> |  <p>TE Part # CAT-M8793-CH8172 MQS, CONNECTOR HOUSING</p> |  <p>TE Part # 1241609-6 SOCKET CONTACT0,63X1,5 AG , LP</p> |  <p>TE Part # 1452157-1 MQS1,5 SOCKET CONTACT</p> |
|  <p>TE Part # 1703033-1 MQS CLEAN BODY EDS LP</p> |  <p>TE Part # 1703033-5 MQS CLEAN BODY EDS LP</p> |  <p>TE Part # 1719532-6 MQS0,63 Au rec CB unseal. AWG18</p> |  <p>TE Part # 1719533-1 MQS CB TERMINAL AWG 18 LP</p> |
|  <p>TE Part # 1719533-5 MQS CB TERMINAL AWG 18 LP</p> |  <p>TE Part # 1719533-6 MQS CB,TERMINAL</p> |  <p>TE Part # 5-968220-7 MQS SOCKET CONTACT</p> |  <p>TE Part # 1241919-1 MQS SOCKET CONTACT CLEAN BODY SHORT</p> |
|  <p>TE Part # 1241921-1 MQS SOCKET CONTACT, LP</p> |  <p>TE Part # 6-968220-6 MQS RECEPTACLE CONTACT</p> |  <p>TE Part # 1241608-2 BU-KONTAKT 0,63X1,5</p> |  <p>TE Part # 1241609-2 BU-KONTAKT 0,63X1,5</p> |



TE Part # 9-968220-1
MQS CLEAN BODY REC CONT

TE Part # 9-968221-1
MQS CLEAN BODY REC CONT

Also in the Series

MQS

Automotive Connector Caps & Covers
(133)

Automotive Connector EMC Shielding
(2)

Automotive Connector Locks & Position Assurance(29)

Automotive Headers(207)

Automotive Housings(498)

Automotive Seals & Cavity Plugs(26)

Automotive Terminals(98)

Data Connectivity Headers(1)

Insertion & Extraction Tools(42)

Other Automotive Connector Accessories(13)

Customers Also Bought

TE Part #1-1579007-6
EXTRACTION TOOL

TE Part #1-1579007-3
EXTRACTION TOOL

TE Part #1-1579007-1
EXTRACTION TOOL

TE Part #1473244-1
MQS, CONNECTOR HOUSING






TE Part #1-1579007-2
EXTRACTION TOOL



TE Part #1-1579018-4
EXTRACTION TOOL



TE Part #1473247-1
MQS 81P LEVER(R) ASSY



TE Part #1-1355133-1
HEBEL F.AUFNAHM-GEH



TE Part #1394872-1
SEALING PLUG 1,5MM



TE Part #NB13414001
RNF-100-3/4-RD-SP

Documents

Product Drawings
EXTRACTION TOOL

English

Datasheets & Catalog Pages
Insertion-Extraction-Tool-2345721-1

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English