




Connectors > D-Shaped Connectors > D-Sub Connectors > Solder D-Sub Connectors



Connector & Housing Type: **Plug**  
Connector System: **Cable-to-Board**  
Number of Positions: **15**  
D-Sub Contact Size: **20**  
D-Sub Shell Size: **2**

Features

Product Type Features

Grade	Standard
Grounding Indents	With
Product Type	Connector
Shell Type	Front Metal Shell
Connector & Housing Type	Plug
Connector System	Cable-to-Board
D-Sub Shell Size	2
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Preloaded	Yes
Number of Positions	15

Body Features

Shell Material	Steel
----------------	-------



Color	Gray
Shell Plating Material	Tin over Nickel

Contact Features

Contact Type	Pin
Contact Mating Area Plating Thickness	.08 µm
Contact Mating Area Plating Material	Gold
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Brass
D-Sub Contact Size	20
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Mechanical Attachment

Mounting Angle	Straight
PCB Mount Retention Type	None
Mating Retention	With
Mating Retention Type	Mounting Holes
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Thermoplastic
Enclosure	Without
Centerline (Pitch)	2.74 mm[.11 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	Yes
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought







TE Part #926097-1  
FF 250 TAB HSG 3P NYLON NAT




TE Part #1-1478762-5  
METAL BACKSHELL 15 WAY TOP E




TE Part #1-2198617-5  
Ni Plated Plastic Backshell, 15 Way, Str



TE Part #1-1393561-9  
V42254A 112V 9=SUB D SCHRAUBE




TE Part #1337771-8  
50 OHM COAX BNC STR PLUG P99-E




TE Part #1337771-4  
50 OHM COAX BNC STR PLUG STR P




TE Part #1393738-3  
V42254A6000G125=SUB D GEHAEUSE



TE Part #1393738-1  
V42254A6000G109=SUB D GEHAEUSE



TE Part #1393738-2  
V42254A6000G115=SUB D GEHAEUSE



TE Part #1-1393738-1  
V42254A6000K115=SUB D GEHAEUSE

Documents

Product Drawings

V42254A1115C215=SUB D STIFTLEI

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_4-1393483-8\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1393483-8\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_4-1393483-8\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[AMPLIMITE Subminiature D Connectors - Subminiature D Connectors for Cable Mounting](#)

English

---

[Product Environmental Compliance](#)

[TE Material Declaration](#)

English