




RAST

TE Internal #: 5-1534796-8

Standard Edge Connectors, Wire-to-Board, 8 Position, 2.5mm [.098in] Centerline, Insulation Displacement Crimp (IDC), 1 Row, Natural Housing Color

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**

Number of Positions: **8**

Centerline (Pitch): **2.5 mm [.098 in]**

Termination Method to Wire & Cable: **Insulation Displacement Crimp (IDC)**

Number of Rows: **1**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Card Entry Style	Side
Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	8
Number of Rows	1
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	250 V
-------------------	-------

Contact Features

Contact Retention Within Housing	With
----------------------------------	------



Contact Type	Socket
Contact Mating Area Plating Material Thickness	3 – 6 µm
Contact Mating Area Plating Material	Tin
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Tin
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)
------------------------------------	-------------------------------------

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Retention	Without
Mating Alignment	With
Contact Retention Type Within Housing	Locking Lance
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Both Ends Open
Centerline (Pitch)	2.5 mm[.098 in]
Housing Color	Natural
Housing Material	PA 6 GF

Dimensions

Connector Height	7.3 mm[.287 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]
Accepts Wire Insulation Diameter Range	1.27 mm[.05 in]
Wire Size	.22 – .35 mm²

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards



UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Method	Box
Packaging Quantity	6776

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 3-1534796-0
AMP DUOPLUG MK2 CONNECTOR 10P



TE Part # 4-1534796-4
AMP DUOPLUG MARK II CONNECTOR 4 POS. KEY






TE Part # 3-1534796-8
AMP DUOPLUG MK2 CONNECTOR 8P





TE Part # 3-1534796-4
AMP DUOPLUG MK2 CONNECTOR 4P S



 TE Part # 3-1534796-3 AMP DUOPLUG MK2 CONNECTOR 3P	 TE Part # 4-1534796-6 AMP DUOPLUG MARK II CONNECTOR 3-20POS	 TE Part # 4-1534799-1 AMP DUOPLUG MARK II CONNECTOR SELE.LOAD	 TE Part # 4-1534799-3 AMP DUOPLUG MARK II CONNEC. SELEC.LOADED
 TE Part # 6-1534796-3 AMP DUOPLUG MK2 CONNECTOR 3P	 TE Part # 7-1534796-0 AMP DUOPLUG MK2 CONNECTOR 10P	 TE Part # 7-1534796-3 AMP DUOPLUG MK2 CONNECTOR 3P	 TE Part # 9-1534796-3 AMP DUOPLUG MK2 CONNECTOR 3P

Customers Also Bought

 TE Part #1217096-2 PL 187 RECEPTACLE 18-14 AWG TPBR	 TE Part #160533-2 110 FASTON,REC.,20-17 AWG,TPBR	 TE Part #175057-1 250 PL EX FLAG REC. 18-12AWG PTBR	 TE Part #1658615-3 IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm
 TE Part #1718475-1 MCON, RECEPTACLE AND TAB	 TE Part #172166-1 3 CIR UNIV M-N-L PLUG	 TE Part #160018-1 RING TONGUE 176 20-16 AWG 0.251 STNP	 TE Part #1-2314812-2 12P,2MM,B-B,REC,DRV,T,2.0,0.1AU,TB, W/CAP
 TE Part #1-282832-3 TERMI-BLOK PIN HEADER 5MM STAC	 TE Part #YDIV44E15-35SNC001 RECP ASSY		

Documents



Product Drawings

AMP DUOPLUG 2,5 MARK II CONNECTOR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1534796-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1534796-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1534796-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST2.5

English

RAST Connector System Catalog

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English