



MICRO-EDGE

TE Internal #: 5822134-3
SIMM Sockets, 22° Module Orientation, 72 Position, Through Hole - Solder, 1.27mm [.05in] Centerline, 1 Row, Printed Circuit Board
[View on TE.com >](#)

Connectors > Socket Connectors > Memory Sockets > SIMM Sockets



Module Orientation: 22°
Number of Positions: 72
PCB Mounting Style: Through Hole - Solder
Centerline (Pitch): 1.27 mm [.05 in]
Number of Rows: 1

Features

Product Type Features

Center Post	With
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Socket
Profile	Low

Configuration Features

Center Key	None
Number of Keys	1
Module Orientation	22°
Number of Positions	72
Number of Rows	1

Body Features

Ejector Location	None
Latch Material	Stainless Steel



Retention Post Location	Center
Latch Plating Material	Nickel

Contact Features

Socket Style	SIMM
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1 A
Contact Mating Area Plating Thickness	200 µin
Socket Type	Memory Card
Contact Mating Area Plating Material	Tin

Termination Features

Insertion Style	Cam-In
Termination Post Length	2.92 mm, 3.56 mm[.115 in][.14 in]

Mechanical Attachment

Polarization	Left
PCB Mounting Style	Through Hole - Solder
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
Housing Material	LCP (Liquid Crystal Polymer)

Dimensions

Center Retention Hole Diameter	1.63 mm[.064 in]
--------------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tube, Tube
------------------	------------------



Packaging Quantity

26

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1759503-1

mini PCI-E 8H Type I PKG G/F

Customers Also Bought



TE Part #1-640457-6
Polyester Right Angle PCB Header:
2.54mm, Unshrouded, MTA 100

TE Part #1-640452-4
Polyester Vertical PCB Header: 2.54
mm, Unshrouded, No Mating
Alignment

TE Part #NB07112001
Single Wall RNF-100 Reel HS Tubing

TE Part #1-148059-5
096 EURO TYP C RECP 17MM ASSY

TE Part #1055689-1
2367 5002 54, VERT PLUG

TE Part #1057463-1
3084 2240 00

TE Part #1-1734101-0
Champ050 series, 100pos, Au over PdNi

TE Part #1393114-3
KUPE-3D17-12=KU

TE Part #1-1546215-2
TERMI-BLOK PCB MOUNT, 90 12P.

TE Part #1-5530843-8
CONN SEC II 30 POS 100C/L

Documents

Product Drawings

72 ME .050 L/P M/L PB-FREE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5822134-3_B_c-5822134-3-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5822134-3_B_c-5822134-3-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5822134-3_B_c-5822134-3-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English

MICRO-EDGE SIMM (Single In-Line Memory Module) Connectors

English

Product Environmental Compliance

TE Material Declaration

English