



Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Tab**
Wire Size: **1.03 – 2.62 mm²**
Quick Disconnect Terminal Orientation: **Straight**
Fully Insulated: **No**

Features

Product Type Features

Sealable	No
Insulated	No

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Unplated

Contact Features

Terminal Type	Tab
Terminal & Splice Type	Tab
Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Accepts Wire Insulation Diameter Range	2.7 – 3.7 mm[.106 – .145 in]
Receptacle Terminal Stock Thickness	.4 mm[.015 in]
Wire Size	1.03 – 2.62 mm²

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	5000
Quick Disconnect Packaging Method	Loose Piece/Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 42098-1
FF 250 TAB 18-14 AWG .032 BR



TE Part # 42460-1
FF 250 TAB 18-14AWG BR



TE Part # 170340-1
FF 250 TAB 20-14AWG BR WITHOUT LATCH



TE Part # 170341-1
FF 250 TAB 14-12AWG BR WITHOUT LATCH



TE Part # 880636-2
FF 250 TAB 1.0-2.5 MM2 0.39 X 13.2 TPBR



TE Part # 60294-1
FF 250 TAB 22-18AWG BR



TE Part # 170349-1
FF 250 TAB 22-20AWG BR WITHOUT LATCH



TE Part # 62553-1
FF 250 TAB 22-18AWG BR



TE Part # 880638-1
FF 110 TAB 1.0-2.5 MM2 0.40 X 14.1 BR



TE Part # 880638-2
.110 SERIES FASTIN-

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(216)



Insertion & Extraction Tools(2)




PCB Terminals(2)




Quick Disconnects(258)


Customers Also Bought



TE Part #350200-1
.140 DIA SOK 14-10 PTPBR



TE Part #350201-1
.140 DIA PIN 14-10 PTPBR



TE Part #444335-1
FASTON 250 REC 1-5 MM2 0.40 X 18.54 BR




TE Part #170262-5
EIS REC CONTACT 20-26







TE Part #881770-1
ECONOSEAL, CONNECTOR
HOUSING



TE Part #180906
FF 250 TAB HSG 6P NYLON NAT



TE Part #350566-3
MINI AMP-IN 22-18 PTPBR



TE Part #348989-1
0.5MM CABLE SEAL LC RED



TE Part #444026-2
RT ANTI ROTATIONAL 1-5 MM2
ELECTRO TPBR

TE Part #2310344-1
1062-12-0166

Documents

Product Drawings

FF 250 TAB 1.0-2.5 MM2 0.39 X 13.2 BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_880636-1_A_c-880636-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_880636-1_A_c-880636-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_880636-1_A_c-880636-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English