



Connectors > Automotive Connectors > Automotive Headers > SUPERSEAL 1.0 HEADERS



Connector System: Wire-to-Board, Wire-to-Device

Number of Positions: 26

Centerline (Pitch): 3 mm [.118 in]

Sealable: Yes

PCB Mount Orientation: Vertical

[All SUPERSEAL 1.0 HEADERS \(23\)](#)

Features

Product Type Features

Hybrid Header	No
Connector System	Wire-to-Board, Wire-to-Device
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Sections	1
Number of Signal Positions	26
Number of Positions	26
PCB Mount Orientation	Vertical
Number of Rows	4

Electrical Characteristics

Voltage Rating (Max)	250 VAC
----------------------	---------



Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 240 V
Operating Voltage	250 VAC

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Mating Pin Diameter	1 mm[.039 in]
Contact Mating Area Plating Material	Gold (Au)

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Locking Interface	With
Mounting Holes	With
PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without

Housing Features

Centerline (Pitch)	3 mm[.118 in]
--------------------	---------------

Dimensions

Profile Height from PCB	24.7 mm[.972 in]
Product Width	39 mm[1.535 in]
Product Length	36.5 mm[1.437 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-40 – 125 °C, -40 – 125 °C[-40 – 257 °F][-40 – 257 °F]

Operation/Application

Shielded	No
----------	----

Industry Standards

Degree of Protection	JIS D0203
UL Flammability Rating	UL 94V-0



Packaging Features

Packaging Type	Tube
----------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | SUPERSEAL 1.0mm



Automotive Headers(24)

Automotive Housings(11)

Automotive Seals & Cavity Plugs(1)

Automotive Terminals(6)

Customers Also Bought

TE Part #1-1623779-7
Wirewound Resistor: Vertical Mount

TE Part #1-1623795-2
Wirewound Resistor: Horizontal Mount

TE Part #106455-3
FF 110 PLUG HSG 8P.

TE Part #1-1703843-1
HEAVY DUTY SEALED CONNECTOR HOUSINGS

TE Part #DRC23-40PB-N012
DEUTSCH DRC HEADERS

TE Part #1376607-1
TH/.025 CONNECTOR SYSTEM,
RECPT AND TAB

TE Part #1473250-1
MQS 81P LEVER(L) ASSY

TE Part #1452409-2
SECONDARY LOCK FOR 58 POS
CONN

TE Part #1452408-2
SECONDARY LOCK FOR 58 POS
CONN

TE Part #1-1740197-2
15P HD20PIN HEADER EUROSTYLE
SMT UNC4-40

Documents

- Product Drawings

SUPER SEAL 26POS CAP ASSY V AU

Japanese
- CAD Files

3D PDF

3D
- Customer View Model

ENG_CVM_CVM_6473418-1_D.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_6473418-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6473418-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Super Seal Connector](#)

Japanese

[Application Specification](#)

Japanese

[Receptacle Contact, Super Seal Connector](#)

Japanese

[Application Specification](#)

Japanese

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[SUPER SEAL CONNECTOR PLUG HOUSING CONNECTOR](#)

English

Agency Approvals

[UL Report](#)

English