




RAST

TE Internal #: 7-1534796-3

Standard Edge Connectors, Wire-to-Board, 3 Position, 2.5mm [.098in] Centerline, Insulation Displacement Crimp (IDC), 1 Row, Natural Housing Color

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Wire-to-Board**
Number of Positions: **3**
Centerline (Pitch): **2.5 mm [.098 in]**
Termination Method to Wire & Cable: **Insulation Displacement Crimp (IDC)**
Number of Rows: **1**

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Card Entry Style	Side
Number of Insulation Displacement Slots	3
Compatible With Wire & Cable Type	Discrete Wire
Number of Positions	3
Number of Rows	1
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	250 V
-------------------	-------

Body Features



Keying Between Cavity Locations	1&2
---------------------------------	-----

Contact Features

Contact Retention Within Housing	With
Contact Type	Socket
Contact Mating Area Plating Material Thickness	3 – 6 µm
Contact Mating Area Plating Material	Tin
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Tin
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)
------------------------------------	-------------------------------------

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Retention	Without
Mating Alignment	With
Contact Retention Type Within Housing	Locking Lance
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Both Ends Open
Centerline (Pitch)	2.5 mm [.098 in]
Housing Color	Natural
Housing Material	PA 6 GF

Dimensions

Connector Height	7.3 mm [.287 in]
PCB Thickness (Recommended)	1.5 mm [.059 in]
Accepts Wire Insulation Diameter Range	1.27 mm [.05 in]
Wire Size	.22 – .35 mm²

Usage Conditions

Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]
-----------------------------	-----------------------------



Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Method	Tray
Packaging Quantity	3850

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer











This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 <p>TE Part # 4-1534796-4 AMP DUOPLUG MARK II CONNECTOR 4 POS. KEY</p>	 <p>TE Part # 1740524-3 AMP DUOPLUG MARK2 CONNECTOR</p>	 <p>TE Part # 2-1534796-3 AMP DUOPLUG MK2 CONNECTOR 3P</p>	 <p>TE Part # 5-1534796-8 AMP DUOPLUG 2,5 MARK II CONNECTOR</p>
 <p>TE Part # 7-1534796-0 AMP DUOPLUG MK2 CONNECTOR 10P</p>	 <p>TE Part # 9-1534796-3 AMP DUOPLUG MK2 CONNECTOR 3P</p>	 <p>TE Part # 2306286-3 3P DUOPLUG MARK II SIDE LOCKING, FUL</p>	

Customers Also Bought

 <p>TE Part #2-1625999-5 Power Resistors: Aluminum Housed, HSC</p>	 <p>TE Part #1-1624094-8 3613C 4.7UH 10%</p>	 <p>TE Part #1622196-1 LR0204 1% 22K</p>	 <p>TE Part #1-1622796-3 YR1 0.1% 1K37</p>
 <p>TE Part #1-1624094-5 3613C 3.3UH 10%</p>	 <p>TE Part #1740533-5 AMP DUOPLUG POW CONN. 5POS W.PCB LOCKING</p>	 <p>TE Part #1-282010-1 AMP MONO-SHAPE TAB CONN 10P.</p>	 <p>TE Part #175020-2 250 POSITIVE REC EX MK-2</p>
 <p>TE Part #1971846-6 6P, RAST 5 Tab Header, THV</p>	 <p>TE Part #EH72726001 DSPL-NR3-X-55MM</p>		

Documents



Product Drawings

AMP DUOPLUG MK2 CONNECTOR 3P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1534796-3_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1534796-3_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1534796-3_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Application Specification

English

Agency Approvals

VDE Certificate

English

VDE Certificate

English