




Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > PCB Latches, Locks & Retainers



Connector & Contact Retention Accessory Type: **Retention Plug**

Contact Current Rating (Max): **3 A**

Circuit Application: **Signal**

Operating Temperature Range: **-65 – 105 °C [-85 – 221 °F]**

Features

Product Type Features

Connector & Contact Retention Accessory Type	Retention Plug
--	----------------

Body Features

Primary Product Material	Polycarbonate GF
Primary Product Color	Red

Contact Features

Contact Current Rating (Max)	3 A
------------------------------	-----

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Box

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 926476-3 MOD 4 HSG	 TE Part # 926476-8 MOD 4 HSG	 TE Part # 926475-3 03P MODU 4 HSG.S.R.	 TE Part # 926475-6 MOD IV HSG SR 6 POS
 TE Part # 926475-4 MOD 4 HSG	 TE Part # 926476-4 2X4P MODU 4 HSG.	 TE Part # 926476-6 MOD 4 HSG	 TE Part # 1-926476-0 MOD 4 HSG



TE Part # 926475-8
MOD 4 HSG



TE Part # 1-926475-0
MOD 4 HSG



TE Part # 1-926476-7
MOD 4 HSG



TE Part # 926475-7
MOD 4 HSG



TE Part # 926475-5
MOD 4 HSG



TE Part # 926476-5
MOD 4 HSG



TE Part # 1-926476-3
MOD 4 HSG



TE Part # 926476-7
MOD 4 HSG



TE Part # 3-926475-0
MOD 4 HSG



TE Part # 926476-9
MOD 4 HSG



TE Part # 1-926475-2
MOD 4 HSG



TE Part # 1-926475-3
MOD 4 HSG


Also in the Series | AMPMODU IV/V



Automotive Headers(2)




Automotive Housings(4)



Backplane Connector Housings(1)




Board-to-Board Connector Contacts(6)



Board-to-Board Headers & Receptacles(937)



Insertion & Extraction Tools(4)



PCB Connector Covers(18)



PCB Connector Keying(6)



PCB Connector Mounting(1)	PCB Connector Strain Relief(3)	PCB Latches, Locks & Retainers(9)	Rectangular Connector Housings(5)
Standard Rectangular Connectors(8)	Wire-to-Board Connector Assemblies & Housings(472)	Wire-to-Board Connector Contacts (328)	

Customers Also Bought

TE Part #1-794617-6 16POS,MICRO MNL,RCPT HSG	TE Part #141708-1 MOD-4 REC.CONT.SCP.	TE Part #1586054-1 VAL-U-LOK PIN BR SN 16AWG	TE Part #926477-3 MOD4 RASTHAKEN
TE Part #1-968968-1 CIRCULAR DIN HOUSINGS	TE Part #1-2141846-1 AMP MCP BACKSHELLS	TE Part #1544228-1 CLIP 8 MM NG1-1 PO	TE Part #1-1393565-7 C42334A 100C 50=RP PASS-STIFT
TE Part #1-1393725-8 C42334A 48A 6=RP622 FEDERLEI	TE Part #1437361-3 185-10=10P 28AWG ST		

Documents



Product Drawings

MOD4 RASTHAKEN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_926478-3_1.3d_igs.zip

English

Customer View Model

ENG_CVM_926478-3_1.3d_stp.zip

English

Customer View Model

ENG_CVM_926478-3_1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English