



Connectors > Automotive Connectors > Automotive Headers > AMPSEAL HEADERS



Connector System: Wire-to-Board, Wire-to-Device

Number of Positions: 23

Centerline (Pitch): 4 mm [.157 in]

Sealable: Yes

PCB Mount Orientation: Vertical

[All AMPSEAL HEADERS \(111\)](#)

Features

Product Type Features

Hybrid Header	No
Connector System	Wire-to-Board, Wire-to-Device
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Sections	1
Number of Signal Positions	23
Number of Positions	23
PCB Mount Orientation	Vertical
Number of Rows	3

Electrical Characteristics

Voltage Rating (Max)	250 VAC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V, 240 V
Operating Voltage	250 VAC

Body Features

Primary Product Color	Black
-----------------------	-------



Contact Features

Mating Tab Width	1.3 mm[.051 in]
Mating Tab Thickness	1.3 mm[.051 in]
Mating Pin Diameter	1.3 mm[.051 in]
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Locking Interface	With
Mounting Holes	With
PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	Without
PCB Mount Retention Type	Solder Tail

Housing Features

Centerline (Pitch)	4 mm[.157 in]
--------------------	---------------

Dimensions

Profile Height from PCB	34.25 mm[1.348 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Product Width	32.1 mm[1.264 in]
Product Length	60.8 mm[2.394 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C[149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Power & Signal

Industry Standards

Degree of Protection	IP6K9K
UL Flammability Rating	UL 94V-0



Packaging Features

Packaging Quantity	1
--------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (1% in Component Part) Dodecamethylcyclohexasiloxane (D6) (1% in Component Part) Decamethylcyclopentasiloxane (D5) (1% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-AM78-CH8172
AMPSEAL HOUSINGS


Also in the Series | AMPSEAL




Automotive Connector Caps & Covers (5)




Automotive Headers(111)



Automotive Housings(16)



Automotive Seals & Cavity Plugs(1)



Automotive Terminals(4)

Customers Also Bought



TE Part #3-2176057-1
Thick Film Resistor: Current Sense



TE Part #207441-7
METRIMATE PIN HEADER ASSY,9P



TE Part #1879233-9
SMW5 R22 5%



TE Part #1563110-1
HEAVY DUTY SEALED CONNECTOR BACKSHELLS



TE Part #967116-1
AMP MCP UNSEALED HEADERS




TE Part #3-1393240-6
RT33L048



TE Part #174263-7
ECONOSEAL-J MK-2 LCOK PLATE 6P



TE Part #1544333-1
LANGUETTE 8MM NG1



Documents

Product Drawings

HDR.ASSY,23 POS VERT. W/GASKET

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_776228-1_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_776228-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_776228-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

AMPSEAL Connector Catalog

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English



[Agency Approvals](#)
[Agency Approval Document](#)
English