



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Receptacle**
Housing Type: **Receptacle**
Number of Crimp Terminal Housing Positions: **2**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Connector System	Wire-to-Board, Wire-to-Wire
Housing Type	Receptacle
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	2
--	---

Body Features

Crimp Terminal Housing Housing Color	Natural
Crimp Terminal Housing Mating Retention	Without
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Receptacle
------------------------	------------



Crimp Terminal Housing Terminal Orientation	Straight
---	----------

Mechanical Attachment

Mating Alignment Type	Polarization
Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Crimp Terminal Housing Centerline	7.4 mm[.291 in]
-----------------------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

Crimp Terminal Housing UL Flammability Rating	UL 94V-2
---	----------

Packaging Features

Packaging Quantity	1
Crimp Terminal Housing Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 154719-1 250 HSG. PL MKI REC. NAT	 TE Part # 926526-1 PL MKI 250 REC HSG 5P NYLON BLACK	 TE Part # 520910-1 POSITIVE LOCK 250 HOUSING NYLON 6/6	 TE Part # 926521-2 PL 250 REC HSG 2P NYLON BLACK
 TE Part # 926522-1 PL 250 REC HSG 2P NYLON BLACK	 TE Part # 1-926522-1 PL 250 REC HSG 2P NYLON BLACK	 TE Part # 185010-2 HEADLIGHT HOUSING HOUSING	 TE Part # 178833-1 POSITIVE LOCK .250 HOUSING RECEPTACLE
 TE Part # 1-2133341-2 250 HSG. PL MKI REC. NAT	 TE Part # 1-926522-2 PL 250 REC HSG 2P NYLON NAT	 TE Part # 174587-1 PL 187 (4.8 MM) HOUSING RECEPTACLE	 TE Part # 926716-1 PL 2P HOUSING PA 6.6 ZYTEL 101 BLACK
 TE Part # 1-2133341-1 PL MK1 RECEPTACLE NATURAL 6.6 PA	 TE Part # 100100-1 2 POS POSITIVE LOCK (PL) HOUSING	 TE Part # 172864-1 250 POSITIVE DBL LOCK 2P NATUR	 TE Part # 926646-3 PL 250 8P HOUSING PA6.6 ZYTEL 101NATURAL

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(203)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(6)



Quick Disconnects(189)


Customers Also Bought



TE Part #1420000-1
MQS, CONNECTOR HOUSING



TE Part #1-2823602-1
PUBLIC SAFETY MIMO LTE ANTENNA




TE Part #1-968968-2
CIRCULAR DIN HOUSINGS



TE Part #1452416-1
58POS CONNECTOR COVER 180 ASSY



TE Part #1-1393387-8
V23540M1050Q570=BUCHSENGEH 50



TE Part #1420001-1
MQS VERSCHL.PLATTE



TE Part #1-1452424-1
BLIND PLUG FOR MCON 1.2 CB (0)



TE Part #154740-2
PIN .175 DIA REC 20-16AWG PB



TE Part #1-1105300-2
HVT-C-Sti.Au.0,5 qmm



TE Part #GV-20
GASKETS FOR SIZE 20 AS CONNECTOR

Documents



Product Drawings

PL 250 REC HSG 2P NYLON NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_926522-2_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_926522-2_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_926522-2_R.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Positive Lock Receptacles

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English