



Connectors > Automotive Connectors > Connector Accessories > Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover**
Strain Relief: **With**
Primary Product Color: **Black**
Primary Product Material: **PA GF**
Number of Positions: **9**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover
---	-------

Configuration Features

Number of Positions	9
---------------------	---

Body Features

Primary Product Color	Black
Primary Product Material	PA GF

Mechanical Attachment

Strain Relief	With
---------------	------

Packaging Features

Packaging Quantity	1500
Packaging Method	Carton

Other

Serviceable	No
-------------	----



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2017 (173) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-967354-1
2.5MM BU-GEH KPL 9P

Also in the Series | Round Connector System



Automotive Connector Caps & Covers (5)



Automotive Housings(16)



Automotive Seals & Cavity Plugs(3)




Automotive Terminals(77)




Insertion & Extraction Tools(8)

Customers Also Bought



TE Part #1633384-5
ANVIL, COMBINATION



TE Part #1746089-1
025/040 44POS COVER V



TE Part #2151975-1
OCEAN_2.0_Applicator-S-093F125OV



TE Part #2266013-1
OCEAN_2.0_APPLICATION-S-050F120O



TE Part #2266535-2
OCEAN_2.0_APPLICATION-S-080F250O




TE Part #1827108-1
025/040 44POS COVER A-TYPE




TE Part #184212-1
2 POS. PLUG ASSY, KEY A



TE Part #W4SD
DEUTSCH DT WEDGELOCKS



TE Part #1123005-2
COVER FOR 2.5 SOCKET HSG 9P



TE Part #1123006-2
2.5MM SOCKET HSG ASSY 9P

Documents



Product Drawings

2,5MM ABDECKKAPPE9P

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_965739-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_965739-1_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_965739-1_A1.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.