

Raychem


TE Internal #: 855366-000

Cable Transitions & Breakouts, Y Shape, 3 Branches , 25, 25,
Adhesive Pre-Coat, Operating Temperature Range -75 – 150 °C
[-103 – 302 °F]

[View on TE.com >](#)



Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**
Number of Branches/Legs: **3**
Material Code: **25**
Breakout & Transition Material Systems Code: **25**
Adhesive Pre-Coat: **Yes**

Features

Product Type Features

Molded Part Shape	Y Shape
Size Code	012

Configuration Features

Number of Branches/Legs	3
-------------------------	---

Body Features

Material	Fluid Resistant Modified Elastomer
Material Code	25
Breakout & Transition Material Systems Code	25
Adhesive Pre-Coat	Yes

Dimensions

Inside Diameter Range (Leg 2)	3.3 – 6.6 mm[.13 – .26 in]
Inside Diameter Range (Body)	6.1 – 13.2 mm[.24 – .52 in]
Inside Diameter Range (Leg 1)	3.3 – 6.6 mm[.13 – .26 in]

Usage Conditions

Operating Temperature Range	-75 – 150 °C[-103 – 302 °F]
-----------------------------	-----------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----



Industry Standards

Government Qualified	No
----------------------	----

Other

Adhesive Code	225
Molded Part Shape Code	382A
Fluid/Chemical Resistance	Long-Term Exposure at High Temperature
Adhesive Options	/225 Precoat
Breakout & Transition Adhesive Type	High Performance Pre-Coat Adhesive
Comment	Use only with DR-25 tubing.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)


Customers Also Bought



TE Part #223494-000
Bulbous Heat Shrink Boots: Lipped, Straight




TE Part #131250-000
Bulbous Heat Shrink Boots: Lipped, Right Angle




TE Part #149069-000
[342A124-25/225-0](#)




TE Part #351271-000
[562A022-25/225-0](#)




TE Part #153282-000
[342A012-25/225-0](#)



TE Part #164153-000
[301A022-25/225-0](#)



TE Part #299698-000
[462A011-25/225-0](#)



TE Part #2820393012
[44A0111-22-9](#)



TE Part #2820293019
[44A0111-20-9](#)



TE Part #BTSH1-21-10-1-B-SB
[BTSH1-21-10-1-B-SB](#)

Documents

Product Drawings

[382A012-25/225-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_-25](#)

English

[Raychem Molded Parts Visual Guide](#)

English



Product Specifications

S1206 PRECOATED LATENT CURE ADHESIVE

English

Product Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet