



Wire Protection & Management > Adhesives & Sealants > Epoxy Adhesives



Epoxy Packaging Method: **Dual Pack**

Epoxy Packaging Quantity: **5**

Heat Resistance Temperature (Max): **150 °C**

Features

Product Type Features

Product Type	Epoxy/Polyamide Two-Part Paste
System	25

Body Features

Color (Supplied)	Black, Gray
------------------	-------------

Usage Conditions

Heat Resistance Temperature (Max)	150 °C
-----------------------------------	--------

Packaging Features

Epoxy Packaging Method	Dual Pack
Epoxy Packaging Quantity	5

Other

Curing Method	20 °C for 24 hr, 85 °C for 1 hr
Pot Life	90 minute
Comment	2-Part Epoxy

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold






EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # CJ2087-000 HL2010E-KIT-120V	 TE Part # 7730454002 HCTE-1250-0-SP	 TE Part # 3679754004 HCTE-1000-0-SP	 TE Part # 1618474004 HCTE-0625-0-SP
 TE Part # 8918194004 HCTE-0750-0-SP	 TE Part # 6638954004 HCTE-0500-0-SP	 TE Part # 6790994004 HCTE-0187-0-SP	 TE Part # 5172334004 HCTE-0281-0-SP




TE Part # 7391174004

[HCTE-0437-0-SP](#)




TE Part # 7662514004

[HCTE-1500-0-SP](#)



TE Part # 2270594002

[HCTE-1625-0-SP](#)



TE Part # 5470284010

[CONVOLEX-1-0-SP](#)



TE Part # 5470014004

[CONVOLEX-1-5/8-0-SP](#)



TE Part # 5470234017

[CONVOLEX-7/16-0-SP](#)




TE Part # 9693274004

[HCTE-1750-0-SP](#)



TE Part # 3774834004

[HCTE-2000-0-SP](#)



TE Part # CL1665-001

[S1125-APPLICATOR](#)

Customers Also Bought



TE Part #3-2176416-2

[9W STD M/OX 5% 1K0](#)



TE Part #1-2176370-8

[RQ 0603 649R 0.1% 10PPM 5K RL](#)



TE Part #1-2176215-4

[CPF A 0402 2K1 0.1% 25PPM 1K RL](#)



TE Part #3-1617028-8

[HFW1106K13M = M39016/6-228M](#)




TE Part #5039254029

[Single Wall DR 25: Heat Shrink Tubing, 2:1 Shrink Ratio](#)




TE Part #1617807-1

[TD229-4001S=TD4R 4 SEC M83726/29-4001S](#)



TE Part #ZPF000000000065430

[AFD 50-10-6 PN 1A](#)



TE Part #410244-000

[202F274-51-20-0](#)



Documents

Product Drawings

S1125-KIT-1

English

Datasheets & Catalog Pages

Adhesives Selection Guide

English

Product Specifications

Thermofit Adhesive S-1125 Epoxy, Flexible

English

Product Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English



[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

French

[Safety Datasheet](#)

French

[Safety Datasheet](#)

French

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

Japanese

[Safety Datasheet](#)

Japanese

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)



[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English