



Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal & Splice Type: **Receptacle**
Mating Tab Width: **5.8 mm, 6.3 mm** [.228 in, .248 in]
Mating Tab Thickness: **.8 mm** [.031 in]
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **15 – 17 AWG**

[All TIMER, RECEPTACLE AND TAB \(354\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance
Automotive Terminal Wire Type	Copper

Contact Features

Typical Current Rating	25 A
Crimp Type	F-Crimp
Terminal & Splice Type	Receptacle
Mating Tab Width	5.8 mm, 6.3 mm[.228 in][.248 in]
Mating Tab Thickness	.8 mm[.031 in]
Automotive Terminal Interface Plating	Tin (Sn)
Contact Termination Area Plating Material	Tin (Sn)

Termination Features

Automotive Terminal Termination Method	Crimp
--	-------

Dimensions

Wire Size	1 – 1.5 mm²
-----------	-------------



Wire Size Search	16 AWG, 17 AWG
Wire Insulation Diameter	2 – 3 mm[.079 – .118 in]

Usage Conditions

Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F]
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Agency/Standard	IEC 664/664A (DIN VDE 0110)
-----------------	-----------------------------

Packaging Features

Packaging Method	Reel
Packaging Quantity	2500

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1579007-4 EXTRACTION TOOL	 TE Part # 4-1579007-3 EXTRACTION TOOL KIT	 TE Part # 2305570-1 TERMINAL CUTTER, SIDE FEED	 TE Part # 2-2151261-1 OCEAN_2.0_Applicator-S-090F140F
 TE Part # 2-2151261-2 OCEAN_2.0_Applicator-S-090F140F	 TE Part # 2151261-1 OCEAN_2.0_Applicator-S-090F140F	 TE Part # 2151261-2 OCEAN_2.0_Applicator-S-090F140F	 TE Part # 7-2151261-1 OCEAN_2.0_Applicator-S-090F140F
 TE Part # 7-2151261-2 OCEAN_2.0_Applicator-S-090F140F	 TE Part # 7-2151261-7 OCEAN_2.0_SPARE_PART_KIT-090F140F		

Also in the Series | Standard Timer

 Automotive Terminals(12)	 Plug & Socket Lighting Connectors(2)	 Wire-to-Board Connector Assemblies & Housings(1)
---	--	---

Customers Also Bought



TE Part #1-1721547-2
PCN 3A/5A SLIM PCB RELAY 3VDC

TE Part #1333202-5
ANVIL, COMBINATION (.062)

TE Part #1241959-4
STD-TIM HSG MKII 4P

TE Part #1-282047-1
AMP MONO-SHAPE P.C.B.CONN7P. GL

TE Part #1534073-2
MULTIFIT MK2 ASSY2P

TE Part #1534415-8
DUOPL POW FEM CON8P

TE Part #1-521253-3
PL MKIII & FASTON 250 HSG 2P NYLON GREEN

TE Part #1-1534073-3
MULTIFIT MK2 ASSY3P

TE Part #1-282042-5
AMP MONO-SHAPE P.C.B.CONN2P. GL

TE Part #969484-8
STD TIM MK2 HSG 3P

Documents

Product Drawings

STC REC 6.3 Contact SRC Sn

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_925575-1_AD.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_925575-1_AD.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_925575-1_AD.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Timer Interconnection System

English

Product Specifications

Application Specification

English

Application Specification

English

Product Environmental Compliance

MD_925575-1_06012018243_dmtec

English

MD_925575-1_06012018243_dmtec

English