



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Wire**

Number of Positions: **8**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying & Polarized Rib Location	None
Number of Positions	8
Number of Rows	1

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without



PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 6.6
Centerline (Pitch)	5 mm[.197 in]
Housing Color	Natural

Dimensions

Connector Length	40 mm[1.574 in]
Connector Height	12.2 mm[.48 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

RAST Version	None
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	1200
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

<p>TE Part # 928343-4 STD TIMER GEH 4P</p>	<p>TE Part # 928343-2 STD-TIM GEH 2P</p>	<p>TE Part # 928343-6 STD-TIM GEH 6P</p>	<p>TE Part # 3-928343-8 STD-TIMER GEH 8P</p>
<p>TE Part # 928343-5 5P STD-TIMER GEH</p>	<p>TE Part # 2-928343-8 STD-TIMER GEH 8P</p>	<p>TE Part # 928343-3 STD-TIMER GEH 3P</p>	<p>TE Part # 1-928343-1 STANDARD TIMER HOUSING</p>
<p>TE Part # 1-928343-2 STANDARD TIMER HOUSING</p>	<p>TE Part # 2-928343-5 5P STD-TIMER GEH</p>	<p>TE Part # 2-928343-7 7P STD-TIMER GEH</p>	<p>TE Part # 3-928343-3 STD TIMER HOUSING 3P</p>



TE Part # 928343-7
7P STD-TIMER GEH

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)



Connector Contacts(12)




Crimp Terminal Housings(41)



Insertion & Extraction Tools(1)



Rectangular Connector Housings(1)



Standard Edge Connectors(36)




Standard Rectangular Connectors(138)



Wire-to-Board Connector Assemblies
& Housings(214)



Wire-to-Board Connector Contacts(2)



Wire-to-Board Headers & Receptacles
(424)

Customers Also Bought



TE Part #1813123-1
LEAVYSEAL MOUNTING
ACCESSORIES



TE Part #1717677-3
AMPSEAL 16 HOUSINGS



TE Part #2-1564526-1
HEAVY DUTY SEALED CONNECTOR
HOUSINGS




TE Part #1703838-1
HEAVY DUTY CONNECTORS FIXING
SLIDES





TE Part #2-111196-9
[026 RCPT SYSTEM 50 30 DPLX](#)



TE Part #185636-1
[PROTECT CAP 2.5MM PLUG](#)

TE Part #CJ6406-000
[222K152-25/225-CS-2065-0](#)

Documents

Product Drawings

[STD-TIMER GEH 8P](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_928343-8_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_928343-8_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_928343-8_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[VDE Certificate](#)

English