


Data Sheet


Type Number	6237	
Designation IEC	---	
System	Li-Manganese dioxide / Organic Electrolyte	
UL Recognition	MH 13654 (N)	
Nominal Voltage	3 V	
Typical Capacity C	1350 mAh	
Load 1.0 kOhm, at 20°C down to 2.0 V		
Weight (approx.)	15 g	
Volume	5,6 ccm	
Coding	Date of Manufacturing Month / Year	
Temperature Ranges	min	max.
Storage	-55°C	70°C
Discharge	-30°C	75°C*
Dimensions	min	max.
Diameter (A)	14,45	14,75
Height (B)	33,10	33,00
Shoulder Diameter[L].....	7,00	
Shoulder Height [M].....	0,60	

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d,7d/w	1000 Ω	Time:	500 h
		Capacity [mAh]:	1350
		Energy [mWh]:	3600

* Contact VARTA if the application is intended to be outside the range of -30°C to +75°C.

Information and contents in this data sheet are for reference purpose only.
They do not constitute any warranty or representation and are subject to change without notice.
For most current information and further details, please contact your VARTA representative.

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst

Subject to change without prior notice!


Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Date of issue: 2014-09-16

Data Sheet


Performance Data:

- Temperature Characteristics***




*Discharge Load 5.6 kΩ

- Operating Voltage vs. load resistance***




*Discharge depth 50%

- Capacity vs. load resistance**



- Discharge Characteristics***



* at room temperature 21°C

- Self-discharge rate < 1% at room temperature
- Storage life > 10 years
- Operating life* > 10 years

* depending on environmental condition and energy consumption

Information and contents in this data sheet are for reference purpose only.
They do not constitute any warranty or representation and are subject to change without notice.
For most current information and further details, please contact your VARTA representative.

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst

Subject to change without prior notice!

Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Date of issue: 2014-09-16