



Connectors > Automotive Connectors > Connector Housings > CIRCULAR DIN HOUSINGS



Connector & Housing Type: **Housing for Female Terminals**

Mating Pin Diameter: **1.5 mm [.059 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **7**

Centerline (Pitch): **11.4 mm [.449 in]**

[All CIRCULAR DIN HOUSINGS \(51\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	On the Terminal

Configuration Features

Blank Cavity Position	6, 7
Number of Positions	7

Electrical Characteristics

Nominal Voltage Architecture	12 V, 24 V, 42 V, 48 V
------------------------------	------------------------

Body Features

Cable Exit Angle	180°
Body Material	Other



Primary Product Color	Black
-----------------------	-------

Connector Code	A
----------------	---

Contact Features

Mating Pin Diameter	1.5 mm[.059 in]
---------------------	-----------------

Mechanical Attachment

Mounting Feature	Without
------------------	---------

Terminal Position Assurance	No
-----------------------------	----

Strain Relief	No
---------------	----

Housing Features

Centerline (Pitch)	11.4 mm[.449 in]
--------------------	------------------

Dimensions

Product Length	31 mm[1.22 in]
----------------	----------------

Product Height	32.8 mm[1.291 in]
----------------	-------------------

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
-----------------------------	---

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Industry Standards

Degree of Protection	IP69K
----------------------	-------

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	500
--------------------	-----

Packaging Method	Box
------------------	-----

Other

Serviceable	No
-------------	----

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 828922-1
2,5MM CAVITY PLUG FOR 5,4MM DI



TE Part # 828904-1
SINGLE WIRE SEAL FOR J.P.T.CON



TE Part # CAT-C4962-CH8172
CIRCULAR DIN HOUSINGS



TE Part # CAT-C4962-B128
CIRCULAR DIN BACKSHELLS



TE Part # CAT-R7602-T273
ROUND CONNECTOR SYSTEM, PIN AND SOCKET



TE Part # 185636-1
PROTECT CAP 2.5MM PLUG



TE Part # 185792-1
180 DEG CAP FOR CORRUGTD TUBE

Customers Also Bought



TE Part #1-967629-5
TIMER, CONNECTOR HOUSING



TE Part #1-968968-3
CIRCULAR DIN HOUSINGS



TE Part #1-968322-1
MQS, CONNECTOR HOUSING



TE Part #1-967588-1
AMP MCP, RECEPTACLE AND TAB



TE Part #1318801-1
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #1-963734-1
TIMER, RECEPTACLE AND TAB



TE Part #1-2840573-2
PCON12, TERMINAL, FAM SLD/UNSLD



TE Part #1208923001
ACW0219-0.75-75(NS)



TE Part #NB09846001
ATUM-19/6-0-50MM

Documents

Product Drawings
1,5MM BU-STE KPL 5P

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_967650-3_G_c-967650-3-g.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_967650-3_G_c-967650-3-g.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_967650-3_G_c-967650-3-g.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English