



M12 Connector

TE Internal #: T4111002081-000

M12 Connector, Standard Circular Connectors, Wire-to-Wire, 8 Position, Sealable, Wire & Cable, 2A Contact Current Rating (Max), Signal, PBT

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors > M12 Field Installable Unshielded



Connector System: **Wire-to-Wire**
Number of Positions: **8**
Sealable: **Yes**
Connector & Contact Terminates To: **Wire & Cable**
Contact Current Rating (Max): **2 A**

[All M12 Field Installable Unshielded \(102\)](#)

Features

Product Type Features

Prewired	No
Product Type	Connector
Accessory Color	Black
Assembly Type	Electrical Connector
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Plug
Shell Type	Plastic

Configuration Features

Factory Installed Backshell	No
Keying	A
Number of Positions	8



Number of Power Positions	0
Number of Signal Positions	8
Contacts Preloaded	Yes

Electrical Characteristics

Operating Voltage	30 VAC
-------------------	--------

Body Features

Peripheral Seal Material	Silicone
Environmental Protection	IP67
O-Ring Material	Silicone
Environmental Protection Type	Elastomer Sealed
Shell Base Material	PBT
Circular Connector Insulation Material Type	Polyamide 66 GF25

Contact Features

Contact Current Rating (Max)	2 A
Reverse Gender	No
Circular Connector Contact Type	Pin

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Mating Alignment	With
Polarization Code	A
Mating Alignment Type	Keyed

Housing Features

Circular Connector Shell Size	20
-------------------------------	----

Dimensions

Wire Size	.05 – .14 mm ²
-----------	---------------------------

Usage Conditions

IP Dust Sealing Level	6
IP Water Sealing Level	IP67
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]

Operation/Application

Durability Rating	100 Cycles
-------------------	------------



Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	HB
------------------------	----

Packaging Features

Packaging Quantity	1
--------------------	---

Other

Field Serviceable	Yes
-------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (4% in Alloy in Copper) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-C73765-M1E
M12 Field Installable Unshielded



TE Part # 1838415-4
M12 Mtl FEMALE PNL CONN. Sldr Rear (Cir)



TE Part # 1838892-4
M12 Mtl FEMALE PNL CONN. PCB Front (Hex)



TE Part # 5-2172071-2
M12.FMLE.PNLREAR.AC0DE.8P. PCBSTAND.STRT



TE Part # 5-2271137-2
M12.FEMALE PNL.AC0DE.S0LDER REAR.8P(AU)



TE Part # 5-2172077-2
M12.FMLE.PNLREAR.AC0DE.8P.PCB. RA.UNSHLD



TE Part # 5-2271143-2
M12 FEMALE PNL.A C0DE.8P.PCB TYPE.(AU)



TE Part # 1838417-4
M12 Mtl FEMALE PNL CONN. PCB Front (Hex)



TE Part # T4131012081-001
M12,REAR MOUNT,FEMALE,A,8P, S0LDER WIRE



TE Part # T4141012081-001
M12,REAR MOUNT,FEMALE,A,8P, S0LDER PCB



TE Part # T4141016081-000
M12,REAR MOUNT,FEMALE,A,8P, M16,P0TTING




TE Part # T4171120008-801
M12,REAR MOUNT,FEMALE,A,8P,0.2 M WIRE




TE Part # T4171120008-802
M12,REAR MOUNT,FEMALE,A,8P,0.5 M WIRE

Also in the Series | M12 Connector




Circular Connector Adapters(2)




Standard Circular Connectors(453)

Customers Also Bought







TE Part #179956-6
DYNAMIC 5000 REC AND TAB CONT




TE Part #1879453-7
Wirewound Resistor: Mineral, 2.5 Kw




TE Part #1-2314101-1
M12 CRIMP CONTACT FOR A8 CODE




TE Part #T4171120008-001
M12 Panel Mount Wire




TE Part #103957-4
4X5 MTE RCPT SR LATCH .100CL




TE Part #1775051-1
MINI USB, TYPE A/B, R/A, SMT, MYLAR




TE Part #1879225-7
CPF 0603 44K2 0.1% 25PPM 1K RL



TE Part #1622796-5
YR1 0.1% 10K2



TE Part #1-2273035-1
M12 A-CODE FEMALE STRAIGHT PIGTAIL



TE Part #1-927995-1
TELFIX CONTACT

Documents

Product Drawings

M12,MALE,STRAIGHT,A CODE,8P,PG9,GOLD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T4111002081-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T4111002081-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T4111002081-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



M8 / M12 Connector System Catalog

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English