


PRODUCT DATA SHEET

3518a

Solderless terminal – 3518 A Cu sn 4-2.5



Product Overview

SKU	3518a
Part description	Solderless terminal
Part designation	3518 A Cu sn 4-2.5

Material

Component	Copper
Surface	Pure tin-plated

Technical Details


Net weight kg/1000	0.604
Conductor cross-section	1.5 – 2.5mm ² / AWG 16-14
Operating temperature max.	125°C
Current rating max.	18A bei 1.5mm ² / AWG 16 (at 20 ° C room temperature)
Current rating max.	30A bei 2.5mm ² / AWG 14 (at 20 ° C room temperature)
UL-No.	E235797

Marking

RoHS, REACH, CRMT	compliant
DIN	n/a

Dimensions

for stud	M4
øD [mm]	4.3
øD1 [mm]	2.3
øD3 [mm]	6.8
L [mm]	11.6
A [mm]	5
R [mm]	4.5
S [mm]	0.8



© 2021 | Vogt AG Verbindungstechnik

The general conditions of sale of Vogt AG apply to this product. See www.vogt.ch.

This data sheet is regularly revised but is not subject to any change service.

This article is a freely available article according to the above specification. The availability of certificates according to SN EN 10204, others acceptance test certificates and customer-specific part submission warrant are to be requested by the customer and, if available, can be obtained for a fee.