





REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 10/04/05'		




N:NUMBER OF CONTACTS



RECOMMEND PCB LAYOUT(TOLERANCE=±0.05)



V/T TYPE



R/A TYPE

NOTES:

1. MATERIAL

- 1.1 INSULATOR:THERMOPLASTIC(UL 94V-0).
- 1.2 CONTACT: COPPER ALLOY.

2. SPECIFICATION

- 2.1 TEMPERATURE:-20°C~+105°C.
- 2.2 CONTACT RESISTANCE:20mΩ max.
- 2.3 INSULATION RESISTANCE:1000MΩ min.
- 2.4 DIELECTRIC WITHSTANDING VOLTAGE:AC 500V PER MINUTE.

3. PART NUMBER: DS1020

4. PRODUCT NUMBER CODE:

DS1020- X X X X

- CONTACT TYPE
D: Double side
- CONTACT PLATING
T1: TIN
- MOUNTING TYPE
S: V/T TYPE
R: R/A TYPE
- No. OF CONTACTS
02~27
- SERIES No.
DS1020

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	FFC/FPC CONNECTOR		
X.	±0.60	X.	±5°	UNITS	mm	PITCH 2.54mm LIF.T/H			
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1020 SERIES		
.XX	±0.25	.XX	±2°	晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD					
DRAWING TYPE		CUSTOMER							
SCALE		1:1	SHEET						1 OF 1
DRAWING NO.		C-DS1020-XXXX							



晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD

Tel:86-574-63508787
Fax:86-574-63510817
E-mail:sale@zhenqin.com.cn
Http://www.connfly.com