

MB912-762M

RoHS
Compliant

UL[®] US







□□ : Poles

762 : Pitch 7.62mm

912 : Standard

MB : Type

PCB Layout



Pitch : 7.62mm(0.300inch)					
Poles	A(mm)	A(inch)	Poles	A(mm)	A(inch)
2	15.24	0.600	15	114.30	4.500
3	22.86	0.900	16	121.92	4.800
4	30.48	1.200	17	129.54	5.100
5	38.10	1.500	18	137.16	5.400
6	45.72	1.800	19	144.78	5.700
7	53.34	2.100	20	152.40	6.000
8	60.96	2.400	21	160.02	6.300
9	68.58	2.700	22	167.64	6.600
10	76.20	3.000	23	175.26	6.900
11	83.82	3.300	24	182.88	7.200
12	91.44	3.600	25	190.50	7.500
13	99.06	3.900			
14	106.68	4.200			

Current rating : 30Amp AC300V
Insulation withstands volt : AC2000V min
Insulation resistance : >2000MΩ DC500V
Operation temperature : -40°C to +105°C
Wire strip length : 8mm
Wire range : 10~24 AWG
Screw torque : 5.5 lb-inch

CONFIRMED & ACCEPTED BY

	Material		Plating/Finish	Remark
1	Insulating body	Polyamide 66(UL94V-0)		Green
2	Cage clamp	Brass	Ni plated	
3	Terminal	Brass	Tin plated	
4	Screw	Steel	Ni plated	

DECA

PART NO.	MB912-762M				VERSION	C	CONFIRMED BY	U. J. J. J. J.
SHEET OF	2/2	METRIC	MM	DRAWN BY	Heiang Ho	DATE	2011/03/02	GENERAL MANAGER

單據編號 : QR-0703-08

版次 : A版

Distributed by Conrad Electronic SE