


Automotive Fuse --- Fast-Acting Type

ASB-L - Blade Terminal Fuse

The intelligent MICRO 2 blade fuse is designed with an indicating device on top which lights up when the fuse is blown further provide the easy identification for blown fuse that needs replacement inside the fuse box assembly.



Unit : mm

Electrical Characteristics :

TIME CURRENT CHARACTERISTICS			
% of Rating	Current Rating	Opening Time	
		Minimum	Maximum
110%	3- 30 Amp	100 Hours	
135%	5- 30 Amp	0.75 Sec	120 Sec
160%	3- 30 Amp	0.3 Sec	50 Sec
200%	3- 30 Amp	0.15 Sec	5 Sec

Patent : Taiwan, Japan and U.S.A.

Color – Coding: Blade Fuses are color-coded for easy amperage identification.

Material: Fuse Body : Thermal Plastic.

Fuse Element : Zinc Alloy


Indicating Device: Single Bi-Polar SMD LED rated at 32V DC Maximum.

Ordering Information:

Catalogue Number	Ampere Rating	Voltage Rating	Color Code	Nominal Resistance Cold Ohms
ASB-L03NY	3	32	Violet	0.031
ASB-L04NY	4	32	Pink	0.023
ASB-L05NY	5	32	Tan	0.017
ASB-L07NY	7.5	32	Brown	0.010
ASB-L10NY	10	32	Red	0.0077
ASB-L15NY	15	32	Blue	0.0049
ASB-L20NY	20	32	Yellow	0.0035
ASB-L25NY	25	32	Natural	0.0026
ASB-L30NY	30	32	Green	0.0021

Marking : Ampere Rating (EX. “30” = 30ampere.)

Time-Current Characteristic Curves



HANSOR PTC